



Part Number : [459858912](#)
Product Description : EXTreme LPHPower Plug, Right-Angle, 8 Power Contacts, Select Gold (Au) Plating, for 3.18mm Thick PC Board, with Guide Pockets
Series Number : 45985
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources

Drawings
[459858912_sd.pdf](#)
[PK-45984-001-001.pdf](#)

3D Models and Design Files
[459858912_stp.zip](#)
[SYM-45985-8912-001.zip](#)

Specifications
[PS-45984-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	45985
Description	EXTreme LPHPower Plug, Right-Angle, 8 Power Contacts, Select Gold (Au) Plating, for 3.18mm Thick PC Board, with Guide Pockets
Application	Board-to-Board, Power
Component Type	PCB Header
Product Name	EXTreme LPHPower
UPC	800756694580

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	23.0A
Voltage - Maximum	250V AC (RMS)/DC (Power)

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	250
First Mate / Last Break	No

Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.047/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	4.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Pitch - Mating Interface	12.00mm
Pitch - Termination Interface	2.00mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	No
(p)ower-(s)ignal Configuration	8p - 0s
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	15
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	230

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme LPHPower Right-Angle PCB Receptacles	<u>45984</u>
12.00mm Pitch EXTreme LPHPower Vertical PCB Receptacles	<u>46112</u>