





**ENGLISH** 

### **Datasheet**

# **Exposed Junction thermocouple with Moulded on Miniature Type K IEC or ANSI Plug**

1, 2 or 3 metres long (IEC584 or ANSI MC96.1 Colour Coded)





- 1, 2 or 3m lengths available
- PFA Teflon® twin twisted pair cable terminating with a moulded on type K IEC/ANSI miniature thermocouple plug
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
- Thermocouple type K with 1/0.3mm or 1/0.5mm conductors
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- IEC584 or ANSI MC96.1 Colour Coded
- Ideal for test & development applications

| T/C<br>Type | Conductors         | Length            |      | +Positive<br>tail wire | -Negative<br>tail wire | Allied<br>code | RS order<br>code     |
|-------------|--------------------|-------------------|------|------------------------|------------------------|----------------|----------------------|
| 'K'         | 1/0.3mm            | 1 metres          | IEC  | Green                  | White                  |                | 131-4752             |
| 'K'         | 1/0.3mm            | 2 metres          | IEC  | Green                  | White                  |                | 131-4753             |
| 'K'<br>'K'  | 1/0.3mm<br>1/0.5mm | 3 metres 1 metres | IEC  | Green                  | White<br>White         |                | 131-4754<br>131-4755 |
| 'K'         | 1/0.5mm            | 2 metres          | IEC  | Green                  | White                  |                | 131-4756             |
| 'K'         | 1/0.5mm            | 3 metres          | IEC  | Green                  | White                  |                | 131-4757             |
| 'K'         | 1/0.3mm            | 1 metres          | ANSI | Yellow                 | Red                    |                | 131-4758             |
| 'K'         | 1/0.3mm            | 2 metres          | ANSI | Yellow                 | Red                    |                | 131-4759             |
| 'K'         | 1/0.3mm            | 3 metres          | ANSI | Yellow                 | Red                    |                | 131-4760             |

## Making your own Thermocouples?

## **L60 Thermocouple & Fine Wire Welder**



The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding

It is primarily designed for use by sensor manufacturers to produce commercial grade thermocouple junctions; it is ideal for producing large numbers of exposed junction thermocouples for test and development laboratories. The L60 Thermocouple Welder is ideally suited to transducer and RTD extension lead attachment

Use of the Thermocouple Welder does not require special skills and most operatives will be capable of producing quality work with little practice. The instrument is supplied with a full range of user accessories including a footswitch

Suitable for use with wires of up to 1.1mm diameter an argon gas shield facility is included but a satisfactory thermocouple junction is produced without the need for argon. The output energy of the L60 Thermocouple Welder can be varied up to 60 Joules

- Simple to use Thermocouple Welder
- Designed for the production of commercial grade thermocouple junctions (See below for range of thermocouple cables)
- Also suitable for other fine wire work
- Front panel or footswitch operation
- Argon gas shield facility

#### Supplied complete with the following accessories:

- Wire Holding Pliers & Lead
- Safety Glasses
- Magnifying Eyeglass
- Carbon Electrodes
- Spare 2A Fuse
- Argon Hose
- Mains Lead
- Footswitch for greater ease of use



Carbon Electrode

#### **ORDERING INFORMATION**

MODELAllied CodeRS ORDER NUMBERFINE WIRE WELDER70825788363-0351Spare Carbon Electrodes (x5) for 1.1mm 250V Fine Wire Welder70656473814-0184RS221/1016

#### **SPECIFICATIONS**

#### General

Energy Output 0-60 Joules Welding Capacity Wires up to 1.1mm diameter Duty Cycle Minimum 5-10 welds/min

#### MECHANICAL

Physical Dimensions 220mm Wide x 120mm High x 250mm Depth Weight 4kg

#### ELECTRICAL

Power Supply 110-120 Vac or 220-250 Vac, 50-60Hz Power Consumption Max 170VA dropping to 20VA during charging

#### **MAINTENANCE**

Apart from keeping the electrode in good order, no other maintenance is required


#### (Front View)



#### (Rear View)



#### **Thermocouple Welder Controls**



| Α | Arc            | Argon gas and weld current controlled by the "Weld" switch. LED indication                 |
|---|----------------|--|
| В | Purge          | Allows the gas line and electrode shield to be purged of air prior to a new welding period |
| С | Weld Switch    | Initiates a welding operation (in "arc" mode also opens the Argon valve)                   |
| D | Argon LED      | Indicates when the Argon control valve is open and gas is flowing                          |
| E | Wait LED       | Glows when weld charge is building   |
| F | Ready LED      | "Ready to Weld" indication   |
| G | Power          | Rotary control of the capacitor charge voltage   |
| Н | Level Selector | Selects the total capacitance available giving the following                               |
|   |                | values with LED indication   |
|   |                |  |
|   |                | "LO" = 0 to 6 Joules   |


"MED" = 0 to 6 Joules "MED" = 0 to 28 Joules "HI" = 0 to 64 Joules

Electrode Holder Holds the replaceable carbon electrode which is accessible by removing the outer Argon Shield

J Red Socket Output socket for using the pliers suppliedK Black Socket Output socket, this provides an additional earth

## **IEC PTFE Insulated Twin Twisted Pair Thermocouple Cable**

Available in Thermocouple Types K, J T & N



Type 'K' Type 'T'

- PTFE twin twisted pair for extending or making simple thermocouples
- Single pair of PTFE insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- 25 & 50 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584-3

| T/C Type | Conductors | Cores         | Reel Length | Allied code | RS order code |
|----------|------------|---------------|-------------|-------------|---------------|
| J        | 1/0.2mm    | +Black/-White | 25 metres   | 70657194    | 827-5980      |
| J        | 1/0.2mm    | +Black/-White | 50 metres   | 70657195    | 827-5984      |
| J        | 1/0.315mm  | +Black/-White | 25 metres   | 70657198    | 827-5993      |
| J        | 1/0.315mm  | +Black/-White | 50 metres   | 70657199    | 827-5996      |
| K        | 1/0.315mm  | +Green/-White | 25 metres   | 70657200    | 827-6000      |
| K        | 1/0.315mm  | +Green/-White | 50 metres   | 70657205    | 827-6019      |
| T        | 1/0.315mm  | +Brown/-White | 25 metres   | 70657208    | 827-6028      |
| Т        | 1/0.315mm  | +Brown/-White | 50 metres   | 70657206    | 827-6022      |
| J        | 1/0.508mm  | +Black/-White | 25 metres   | 70657197    | 827-5990      |
| J        | 1/0.508mm  | +Black/-White | 50 metres   | 70657201    | 827-6003      |
| K        | 1/0.508mm  | +Green/-White | 25 metres   | 70657203    | 827-6012      |
| K        | 1/0.508mm  | +Green/-White | 50 metres   | 70657204    | 827-6016      |
| J        | 7/0.2mm    | +Black/-White | 25 metres   | 70657202    | 827-6006      |
| K        | 7/0.2mm    | +Green/-White | 25 metres   | 70657207    | 827-6025      |
| T        | 7/0.2mm    | +Brown/-White | 25 metres   | 70657209    | 827-6031      |
| N        | 7/0.2mm    | +Pink/-White  | 25 metres   | 70657210    | 827-6034      |

## IEC PVC Insulated Flat Pair Thermocouple Extension & Compensating Cable

PVC Insulated Flat Pair (to IEC-584)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, T & N
- Compensating types VX (KCB) & U (RCA) for types K & R/S Thermocouples respectively

- Stranded conductors available, either 7/0.2mm or 13/0.2mm
- Available in 10, 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to IEC-584-3

|            | Conductors | Cores         | Jacket | Reel Length | Allied<br>Code | RS order code |  |  |
|------------|------------|---------------|--------|-------------|----------------|---------------|--|--|
| Extension: |            |               |        |             |                |               |  |  |
| KX         | 7/0.2mm    | +Green/-White | Green  | 10 metres   | 70657084       | 827-5615      |  |  |
| KX         | 7/0.2mm    | +Green/-White | Green  | 25 metres   | 70641729       | 236-3820      |  |  |
| KX         | 7/0.2mm    | +Green/-White | Green  | 50 metres   | 70657085       | 827-5619      |  |  |
| KX         | 7/0.2mm    | +Green/-White | Green  | 100 metres  | 70646156       | 611-7889      |  |  |
| KX         | 7/0.2mm    | +Green/-White | Green  | 200 metres  | 70657088       | 827-5628      |  |  |
|            |            |               |        |             |                |               |  |  |
|            |            |               |        |             |                |               |  |  |
| JX         | 7/0.2mm    | +Black/-White | Black  | 10 metres   | 70641640       | 219-4753      |  |  |
| JX         | 7/0.2mm    | +Black/-White | Black  | 25 metres   | 70657078       | 827-5592      |  |  |
| JX         | 7/0.2mm    | +Black/-White | Black  | 50 metres   | 70657079       | 827-5596      |  |  |
| JX         | 7/0.2mm    | +Black/-White | Black  | 100 metres  | 70641737       | 236-3915      |  |  |
| JX         | 7/0.2mm    | +Black/-White | Black  | 200 metres  | 70657081       | 827-5606      |  |  |
|            |            |               |        |             |                |               |  |  |
|            |            |               | _      |             |                |               |  |  |
| TX         | 7/0.2mm    | +Brown/-White | Brown  | 10 metres   | 70641637       | 219-4703      |  |  |
| TX         | 7/0.2mm    | +Brown/-White | Brown  | 25 metres   | 70641734       | 236-3870      |  |  |
| TX         | 7/0.2mm    | +Brown/-White | Brown  | 50 metres   | 70657095       | 827-5653      |  |  |
| TX         | 7/0.2mm    | +Brown/-White | Brown  | 100 metres  | 70651749       | 762-1146      |  |  |
| TX         | 7/0.2mm    | +Brown/-White | Brown  | 200 metres  | 70657098       | 827-5662      |  |  |
|            | - 10 -     | / · · · · ·   |        |             |                |               |  |  |
| NX         | 7/0.2mm    | +Pink/-White  | Pink   | 10 metres   | 70641635       | 219-4668      |  |  |
| NX         | 7/0.2mm    | +Pink/-White  | Pink   | 25 metres   | 70657091       | 827-5637      |  |  |
| NX         | 7/0.2mm    | +Pink/-White  | Pink   | 50 metres   | 70657089       | 827-5631      |  |  |
| NX         | 7/0.2mm    | +Pink/-White  | Pink   | 100 metres  | 70657092       | 827-5640      |  |  |

|               | Conductors | Cores          | Jacket | Reel Length | Allied<br>Code | RS order code |
|---------------|------------|----------------|--------|-------------|----------------|---------------|
| Compensating: |            |                |        |             |                |               |
| VX (KCB)      | 7/0.2mm    | +Green/-White  | Green  | 10 metres   | 70657082       | 827-5609      |
| VX (KCB)      | 7/0.2mm    | +Green/-White  | Green  | 25 metres   | 70641629       | 219-4551      |
| VX (KCB)      | 7/0.2mm    | +Green/-White  | Green  | 50 metres   | 70657080       | 827-5603      |
| VX (KCB)      | 7/0.2mm    | +Green/-White  | Green  | 100 metres  | 70641630       | 219-4573      |
| VX (KCB)      | 7/0.2mm    | +Green/-White  | Green  | 200 metres  | 70657083       | 827-5612      |
|               |            |                |        |             |                |               |
| VX (KCB)      | 13/0.2mm   | +Green/-White  | Green  | 10 metres   | 70657086       | 827-5621      |
| VX (KCB)      | 13/0.2mm   | +Green/-White  | Green  | 25 metres   | 70657087       | 827-5625      |
| VX (KCB)      | 13/0.2mm   | +Green/-White  | Green  | 50 metres   | 70657090       | 827-5634      |
| VX (KCB)      | 13/0.2mm   | +Green/-White  | Green  | 100 metres  | 70651750       | 762-1152      |
|               |            |                |        |             |                |               |
| U (RCA)       | 7/0.2mm    | +Orange/-White | Orange | 10 metres   | 70657096       | 827-5656      |
| U (RCA)       | 7/0.2mm    | +Orange/-White | Orange | 25 metres   | 70646158       | 611-7902      |
| U (RCA)       | 7/0.2mm    | +Orange/-White | Orange | 50 metres   | 70657097       | 827-5659      |
|               |            |                |        |             |                |               |
| U (RCA)       | 13/0.2mm   | +Orange/-White | Orange | 10 metres   | 70641641       | 219-4769      |
| U (RCA)       | 13/0.2mm   | +Orange/-White | Orange | 25 metres   | 70657093       | 827-5643      |
| U (RCA)       | 13/0.2mm   | +Orange/-White | Orange | 50 metres   | 70657094       | 827-5647      |
|               |            |                |        |             |                |               |

## **IEC PTFE Single Shot Thermocouple Cable**

Type K, 10 metre reel




- Thermocouple type K
- 10 metre spool length
- 7/0.2mm diameter conductor
- Operating range: -75°C to +250°C
- Teflon insulated single shot construction
- Resistant to chemicals, oils and fliuds
- Suitable for aerospace applications and is widly used in autoclaves
- Colour coded to IEC-584-3

| Туре | Outer       | Length    | Allied code | RS Code  |
|------|-------------|-----------|-------------|----------|
| K    | Green/White | 10 metres | 70657216    | 827-6053 |

## **ANSI PFA Insulated Twin Twisted Pair Thermocouple Cable**

Available in Thermocouple Types K & T (ANSI MC96.1)




- PFA Teflon® twin twisted pair for extending or making simple thermocouples
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
- Thermocouple types K & T with 1/0.2mm OR 1/0.3 conductors. 7/0.2mm option available for type K
- 25, 50 & 100 metre reel lengths
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to ANSI MC96.1

RS221/1016

| T/C Type | Conductors | Cores        | Reel Length 25 metres 50 metres 100 metres | Allied code | RS order code |
|----------|------------|--------------|--|-------------|---------------|
| KX       | 1/0.2mm    | +Yellow/-Red |  | 70656106    | 814-0030      |
| KX       | 1/0.2mm    | +Yellow/-Red |  | 70656111    | 814-0049      |
| KX       | 1/0.2mm    | +Yellow/-Red |  | 70656109    | 814-0042      |
| KX       | 7/0.2mm    | +Yellow/-Red | 25 metres                                  | 70656110    | 814-0046      |
| KX       | 7/0.2mm    | +Yellow/-Red | 50 metres                                  | 70656113    | 814-0055      |
| KX       | 7/0.2mm    | +Yellow/-Red | 100 metres                                 | 70656114    | 814-0058      |
| KX       | 1/0.3mm    | +Yellow/-Red | 25 metres                                  | 70656104    | 814-0024      |
| KX       | 1/0.3mm    | +Yellow/-Red | 50 metres                                  | 70656107    | 814-0033      |
| KX       | 1/0.3mm    | +Yellow/-Red | 100 metres                                 | 70656108    | 814-0036      |
| TX       | 1/0.3mm    | +Blue/-Red   | 25 metres                                  | 70656121    | 814-0080      |
| TX       | 1/0.3mm    | +Blue/-Red   | 50 metres                                  | 70656126    | 814-0099      |
| TX       | 1/0.3mm    | +Blue/-Red   | 100 metres                                 | 70656124    | 814-0092      |
| TX       | 1/0.2mm    | +Blue/-Red   | 25 metres                                  | 70656125    | 814-0096      |
| TX       | 1/0.2mm    | +Blue/-Red   | 50 metres                                  | 70656128    | 814-0106      |
| TX       | 1/0.2mm    | +Blue/-Red   | 100 metres                                 | 70656129    | 814-0109      |

## **ANSI PVC Thermocouple Extension & Compensating Cable**

PVC Insulated Flat Pair (ANSI MC96.1)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, & T
- Compensating types VX (KCB) for types K Thermocouples
- Stranded conductors available, 7/0.2mm
- Available in 25, 100 & 200 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to ANSI MC96.1

| T/C Type          | Conductors | Cores        | Jacket | Reel Length | Allied<br>code | RS order code |  |
|-------------------|------------|--------------|--------|-------------|----------------|---------------|--|
| <b>Extension:</b> |            |              |        |             |                |               |  |
| KX                | 7/0.2mm    | +Yellow/-Red | Yellow | 25 m        | 70656102       | 814-0018      |  |
| KX                | 7/0.2mm    | +Yellow/-Red | Yellow | 100 m       | 70656105       | 814-0027      |  |
| KX                | 7/0.2mm    | +Yellow/-Red | Yellow | 200 m       | 70656103       | 814-0020      |  |
| JX                | 7/0.2mm    | + White/-Red | Black  | 25 m        | 70656096       | 813-9995      |  |
| JX                | 7/0.2mm    | + White/-Red | Black  | 100 m       | 70656098       | 814-0005      |  |
| JX                | 7/0.2mm    | + White/-Red | Black  | 200 m       | 70656099       | 814-0008      |  |
| TX                | 7/0.2mm    | +Blue/-Red   | Blue   | 25 m        | 70656119       | 814-0074      |  |
| TX                | 7/0.2mm    | +Blue/-Red   | Blue   | 100 m       | 70656122       | 814-0083      |  |
| TX                | 7/0.2mm    | +Blue/-Red   | Blue   | 200 m       | 70656123       | 814-0086      |  |
| Compensating:     |            |              |        |             |                |               |  |
| VX (KCB)          | 7/0.2mm    | +Yellow/-Red | Yellow | 25 m        | 70656127       | 814-0103      |  |
| VX (KCB)          | 7/0.2mm    | +Yellow/-Red | Yellow | 100 m       | 70656130       | 814-0112      |  |
| VX (KCB)          | 7/0.2mm    | +Yellow/-Red | Yellow | 200 m       | 70656131       | 814-0115      |  |