NX-series Analog Output Unit

NX-DA

CSM NX-DA DS F 1 1

Wide Lineup to Meet Various Analog Control Needs: from High-speed Synchronous Control to General Purpose


- NX-series Analog Output Unit
- This unit can be used as an ECAT slave by connecting with the ECAT Coupler.
- Voltage and current output models are available.



Features

- Output up to four analog signals with one Unit.
- Free-run refreshing or I/O synchronous refreshing can be selected for refreshing with the EtherCAT Coupler Unit.
- The lineup includes the model which achieves sampling speed of 10 µs and resolution of 1/30000, ideal for high-speed, high-precision control.
- The removable screwless terminal block improves maintenance.
- · Screw-less clamp terminal block significantly reduces wiring work.
- 12-mm-wide unit can save space.

System Configuration



^{*} OMRON CJ1W-NC 81/ 82 Position Control Units cannot be connected to the EtherCAT Slave Terminal even though they support EtherCAT.

Sysmac® is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT® is a registered trademark of Beckhoff Automation GmbH for their patented technology. Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

Ordering Information

International Standards

- The standards are abbreviated as follows: U: UL, U1: UL (Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, CE: EC Directives, and KC: KC Registration.
- Contact your OMRON representative for further details and applicable conditions for these standards.

Analog Output Unit

	Product Name				Specification	on					
Unit type		Capacity	Input range	Resolution	Output setting value, decimal number (0 to 100%)	Over all accuracy (25°C)	Conversion time	I/O refreshing method	NX Unit power Mo consumption	Model	Standards
NX Series				1/8000	-4000 to 4000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	1.10W max.	NX-DA2603	
	Voltage Output Unit	2 points	-10 to	1/30000	-15000 to 15000	±0.1% (full scale)	10 μs/point	Switching Synchronous I/O refreshing and Free-Run refreshing	1.10W max.	NX-DA2605	
		4 points	+10V	1/8000	-4000 to 4000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	1.25W max.	NX-DA3603	
				1/30000	-15000 to 15000	±0.1% (full scale)	10 μs/point	Switching Synchronous I/O refreshing and Free-Run refreshing	1.25W max.	NX-DA3605	UC1.CE,KC
Analog Output Unit	Current Output Unit			1/8000	0 to 8000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	1.75W max.	NX-DA2203	UC1,CE,KC
		2 points	4 to	1/30000	0 to 30000	±0.1% (full scale)	10 μs/point	Switching Synchronous I/O refreshing and Free-Run refreshing	1.75W max.	NX-DA2205	
			20mA	1/8000	0 to 8000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	1.80W max.	NX-DA3203	
	22 22	4 points		1/30000	0 to 30000	±0.1% (full scale)	10 μs/point	Switching Synchronous I/O refreshing and Free-Run refreshing	1.80W max.	NX-DA3205	

Option

Product Name	Specification	Model	Standards
Cording Pins	For 10 Units (Terminal Block: 30 pins, Unit: 30 pins)	NX-AUX02	

Accessories

Not included.

General Specification

	Item	Specification	
Enclosure		Mounted in a panel	
Grounding method		Ground to 100 Ω or less	
	Ambient operating temperature	0 to 55°C	
	Ambient operating humidity	10% to 95% (with no condensation or icing)	
	Atmosphere	Must be free from corrosive gases.	
	Ambient storage temperature	-25 to 70°C (with no condensation or icing)	
	Altitude	2,000 m max.	
	Pollution degree	2 or less: Conforms to JIS B3502 and IEC 61131-2.	
Operating environment	Noise immunity	2 kV on power supply line (Conforms to IEC61000-4-4.)	
environinent	Overvoltage category	Category II: Conforms to JIS B3502 and IEC 61131-2.	
	EMC immunity level	Zone B	
	Vibration resistance	Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz, acceleration of 9.8 m/s², 100 min each in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total)	
	Shock resistance	IConforms to IEC 60068-2-27. 147 m/s², 3 times each in X, Y, and Z directions	
Applicable standards		cULus: Listed UL508 and ANSI/ISA 12.12.01 EC: EN 61131-2 and C-Tick, KC Registration	

3

Analog Output Unit Specifications

Voltage Output Unit 2points NX-DA2603

Unit name	Voltage Output Unit	Model	NX-DA2603		
Capacity	2 points	External connection terminals	Screwless clamping terminal block (8 terminals)		
I/O refreshing method	Free-Run refreshing				
	TS indicator	Output range	-10 to +10 V		
	AD2603 ■TS	Output conversion range	-5 to 105% (full scale)		
		Allowable load resistance	5 kΩ min.		
Indicator		Output impedance	0.5 Ω max.		
		Resolution	1/8000 (full scale)		
		Overall 25°C	±0.3% (full scale)		
		accuracy 0 to 55°C	±0.5% (full scale)		
		Conversion time	250 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	$20~\text{M}\Omega$ min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.10 W max.	I/O current consumption	No consumption		
Weight	70 g max.				
Circuit layout	NX bus connector (left) I/O power supply + I/O power supply -	alit internal GND AG	Output V1+ to V2+ IOG I/O power supply + I/O power supply - I/O power supply - I/O power supply -		
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: No restrictions				
Terminal connection diagram	Additional I/O Power Supply Unit NX-DA2603 A1 B1 V1+ V2+ Voltage Output Unit NX-DA2603 A1 V1+ V2+ Voltage output + Voltage output - Voltage				

Voltage Output Unit 2points NX-DA2605

Unit name	Voltage Output Unit	Model	NX-DA2605		
Capacity	2 points	External connection terminals	Screwless clamping terminal block (8 terminals)		
I/O refreshing method	Switching Synchronous I/O refreshing and	Free-Run refreshing			
	TS indicator	Output range	-10 to +10 V		
	DA2605 ■TS	Output conversion range	-5 to 105% (full scale)		
		Allowable load resistance	5 kΩ min.		
Indicator		Output impedance	$0.5~\Omega$ max.		
		Resolution	1/30000 (full scale)		
		Overall 25°C	±0.1% (full scale)		
		accuracy 0 to 55°C	±0.3% (full scale)		
		Conversion time	10 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	20 M Ω min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.10 W max.	I/O current consumption	No consumption		
Weight	70 g max.				
Circuit layout	NX bus connector (left) NX bus connector (left) NX bus connector l/O power supply -	AMP W	Output V1+ to V2+ IOG I/O power supply + I/O power supply - I/O power supply - I/O power supply -		
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: No restrictions				
Terminal connection diagram	Additional I/O Power Supply Unit NX-DA2605 A1 B1 V1+ V2+ Voltage output + Voltage output + Voltage output -				

Voltage Output Unit 4points NX-DA3603

Unit name	Voltage Output Unit	Model	NX-DA3603		
Capacity	4 points	External connection terminals Screwless clamping terminal block (12 terminals)			
I/O refreshing method	Free-Run refreshing				
	TS indicator AD3603 ■TS	Output range Output conversion range	-10 to +10 V -5 to 105% (full scale)		
		Allowable load resistance	5 kΩ min.		
Indicator		Output impedance	$0.5~\Omega$ max.		
		Resolution	1/8000 (full scale)		
		Overall 25°C	±0.3% (full scale)		
		accuracy 0 to 55°C	±0.5% (full scale)		
		Conversion time	250 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	20 $\text{M}\Omega$ min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.25 W max.	No consumption			
Weight	70 g max.				
Circuit layout	NX bus connector (left) NX bus connector (left) N/O power supply +	AMP W	Output V1+ to V4+ IOG I/O power supply + I/O power supply - I/O power supply -		
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: No restrictions				
Terminal connection diagram	Additional I/O Power Supply Unit A1 IOV IOV IOV IOV IOG IOG IOG IOG A8 B8	Power Supply Unit NX-DA3603			

Voltage Output Unit 4points NX-DA3605

Unit name	Voltage Output Unit	Model	NX-DA3605		
Capacity	4 points	External connection terminals	Screwless clamping terminal block (12 terminals)		
I/O refreshing method	Switching Synchronous I/O refreshing and	Free-Run refreshing			
	TS indicator	Output range	-10 to +10 V		
	DA3605 ■TS	Output conversion range	-5 to 105% (full scale)		
		Allowable load resistance	5 kΩ min.		
Indicator		Output impedance	0.5 Ω max.		
		Resolution	1/30000 (full scale)		
		Overall 25°C	±0.1% (full scale)		
		accuracy 0 to 55°C	±0.3% (full scale)		
		Conversion time	10 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	20 M Ω min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.25 W max.	I/O current consumption	No consumption		
Weight	70 g max.				
Circuit layout	NX bus connector (left) NX bus connector (left) I/O power supply -	AMP (W)	Output V1+ to V4+ IOG I/O power supply + I/O power supply - I/O power supply -		
Installation orientation and restrictions	Installation orientation: Possible in 6 oriental Restrictions: No restrictions	ations.			
Terminal connection diagram	Additional I/O Power Supply Unit NX-DA3605 A1				

Current Output Unit 2points NX-DA2203

Unit name	Current Output Unit	Model	NX-DA2203		
Capacity	2 points	External connection terminals Screwless clamping terminal block terminals)			
I/O refreshing method	Free-Run refreshing	1-			
	TS indicator DA2203	Output conversion	4 to 20 mA -5 to 105% (full scale)		
	-13	range Allowable load resistance	600 Ω min.		
Indicator		Resolution	1/8000 (full scale)		
		Overall 25°C	±0.3% (full scale)		
		accuracy 0 to 55°C	±0.6% (full scale)		
		Conversion time	250 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	20 M Ω min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.75 W max.	I/O current consumption	No consumption		
Weight	70 g max.				
Circuit layout	NX bus connector (left) NX bus connector (left) NX bus connector (left)	auit internal GND AG	Output I1+ to I2+ IOG I/O power supply + I/O power supply - I/O power supply - I/O power supply -		
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: For upright installation: No restrictions For any installation other than upright: Restricted as shown in the graph below.				
Terminal connection diagram	Additional I/O Power Supply Unit NX-DA2203 A1 II+ I2+ IOV IOV IOV IOG IOG NC				

Current Output Unit 2points NX-DA2205

Unit name	Current Output Unit	Model	NX-DA2205		
Capacity	2 points	External connection terminals	Screwless clamping terminal block (8 terminals)		
I/O refreshing method	Switching Synchronous I/O refreshing and	Free-Run refreshing			
	TS indicator	Output range	4 to 20 mA		
	DA2205 ■TS	Output conversion range	-5 to 105% (full scale)		
Indicator		Allowable load resistance	600 Ω min.		
		Resolution	1/30000 (full scale)		
		Overall 25°C	±0.1% (full scale)		
		accuracy 0 to 55°C	±0.3% (full scale)		
		Conversion time	10 μs/point		
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)		
Insulation resistance	$20~\text{M}\Omega$ min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.		
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.		
NX Unit power consumption	1.75 W max.	I/O current consumption	No consumption		
Weight	70 g max.				
Circuit layout	NX bus connector (left) I/O power supply + Olympia I/O power supply - O	uit internal GND AG	Output I1+ to I2+ IOG I/O power supply + NX bus connector (right)		
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: For upright installation: No restrictions For any installation other than upright: Restricted as shown in the graph below. (Q) (1904 600 000 000 000 000 000 000 000 000 000				
Terminal connection diagram	Additional I/O Power Supply Unit A1 B1 OIOV IOV IOV IOV IOG IOG A8 B8 A8	101/ 101/	Current output + Current output –		

Current Output Unit 4points NX-DA3203

Unit name	Current Output Unit	Model		NX-DA3203	
Capacity	4 points	External connection		Screwless clamping terminal block (12	
I/O refreshing method	Free-Run refreshing	terminals		terminals)	
//O refreshing method	TS indicator	Output range		4 to 20 mA	
	DA3203	Output conversion range		-5 to 105% (full scale)	
Indicator		Allowable lo	oad	350 $Ω$ min.	
indicator		Resolution		1/8000 (full scale)	
		Overall	25°C	±0.3% (full scale)	
		accuracy	0 to 55°C	±0.6% (full scale)	
		Conversion	time	250 μs/point	
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation me	ethod	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)	
Insulation resistance	20 MΩ min. between isolated circuits (at 100 VDC)	Dielectric s		510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.	
I/O power supply method	Supply from the NX bus	Current cap	pacity of I/O	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.	
NX Unit power consumption	1.80 W max.		consumption	No consumption	
Weight	70 g max.				
Circuit layout	NX bus connector (left) NX bus connector (left) NX bus connector (left) NX bus connector (right) NX bus connector (right)			Output I1+ to I4+ Terminal block I/O power supply + NX bus connector	
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: For upright installation: No restrictions For any installation other than upright: Restricted as shown in the graph below.				
Terminal connection diagram	Additional I/O Power Supply Unit NX-DA3203 A1				

Current Output Unit 4points NX-DA3205

Unit name	Current Output Unit	Model	NX-DA3205	
Capacity	4 points	External connection terminals	Screwless clamping terminal block (12 terminals)	
I/O refreshing method	Switching Synchronous I/O refreshing and	_	14 to 00 mA	
	TS indicator DA3205 TS	Output range Output conversion range	4 to 20 mA -5 to 105% (full scale)	
Indicator		Allowable load resistance	350 Ω min.	
indicator		Resolution	1/30000 (full scale)	
		Overall 25°C	±0.1% (full scale)	
		accuracy 0 to 55°C	±0.3% (full scale)	
		Conversion time	10 μs/point	
Dimensions	12 (W) x 100 (H) x 71 (D)	Isolation method	Between the input and the NX bus: Power = Transformer, Signal = Digital isolator (no isolation between inputs)	
Insulation resistance	20 M Ω min. between isolated circuits (at 100 VDC)	Dielectric strength	510 VAC between isolated circuits for 1 minute at a leakage current of 5 mA max.	
I/O power supply method	Supply from the NX bus	Current capacity of I/O power supply terminal	IOV: 0.1 A/terminal max., IOG: 0.1 A/terminal max.	
NX Unit power consumption	1.80 W max.	I/O current consumption	No consumption	
Weight	70 g max.			
Circuit layout	NX bus connector (left) NX bus connector (left) NX bus connector (right) NX bus connector (right)			
Installation orientation and restrictions	Installation orientation: Possible in 6 orientations. Restrictions: For upright installation: No restrictions For any installation other than upright: Restricted as shown in the graph below.			
Terminal connection diagram	Additional I/O Power Supply Unit Additional I/O Power Supply Unit NX-DA3205 A1			

Version Information


NX Series Analog Output Unit and Sysmac Studio

NX Series Analog Output Unit	Sysmac Studio		
NA Series Analog Output Onit	Version 1.05 or lower	Version 1.06 or higher	
NX-DA	Not supported	Supported	

External Interface


Analog Output Unit

NX-DA□□□□ 12mm Width



Symbol	Name	Function
(A)	(A) NX bus connector This connector is used to connect each Unit.	
(B)	Indicators	The indicators show the current operating status of the Unit.
(C)	Terminal block The terminal block is used to connect external devices. The number of terminals depends on the type of Unit.	

Terminal Blocks



Symbol	Name	Function
(A)	Terminal number indications Terminal number for which A to D indicate the column, and 1 to 8 indicate the line are display the terminal number is a combination of column and line, so A1 to A8 and B1 to B8 are display the terminal number indications are the same regardless of the number of terminals on the terminal number indications are the same regardless.	
(B)	Release holes	Insert a flat-blade screwdriver into these holes to connect and remove the wires.
(C)	(C) Terminal holes The wires are inserted into these holes.	

Applicable Wires

Using Ferrules

If you use ferrules, attach the twisted wires to them.

Observe the application instructions for your ferrules for the wire stripping length when attaching ferrules.

Always use one-pin ferrules. Do not use two-pin ferrules.


The applicable ferrules, wires, and crimping tool are given in the following table.

Terminal types	Manufacturer	Ferrule model number	Applicable wire (mm² (AWG))	Crimping tool
Terminals other	Phoenix Contact	AI0,34-8	0.34 (#22)	Phoenix Contact (The figure in parentheses is the applicable wire size.)
than ground terminals		AI0,5-8	0.5 (#20)	CRIMPFOX 6 (0.25 to 6 mm ² , AWG24 to 10)
terminais		AI0,5-10		
		AI0,75-8	0.75 (#18)	
		AI0,75-10		
		AI1,0-8	1.0 (#18)	
		AI1,0-10		
		AI1,5-8	1.5 (#16)	
		AI1,5-10		
Ground terminals		Al2,5-10	2.0 *	
Terminals other	Weidmuller	H0.14/12	0.14 (#26)	Weidmuller (The figure in parentheses is the applicable wire size.)
than ground terminals		H0.25/12	0.25 (#24)	PZ6 Roto (0.14 to 6 mm ² , AWG 26 to 10)
terminais		H0.34/12	0.34 (#22)	
		H0.5/14	0.5 (#20)	
		H0.5/16		
		H0.75/14	0.75 (#18)	
		H0.75/16		
		H1.0/14	1.0 (#18)	
		H1.0/16		
		H1.5/14	1.5 (#16)	
		H1.5/16		

^{*} Some AWG 14 wires exceed 2.0 mm² and cannot be used in the screwless clamping terminal block.

When you use any ferrules other than those in the above table, crimp them to the twisted wires so that the following processed dimensions are achieved.


Finished Dimensions of Ferrules



Using Twisted Wires/Solid Wires

If you use the twisted wires or the solid wires, the applicable wire range and conductor length (stripping length) are as follows. Use the twisted wires to connect the ground wire to a ground of 100Ω or less. Do not use the solid wires.


Terminal types	Applicable wires	Conductor length (stripping length)	
Ground terminals	2.0 mm ²	9 to 10 mm	
Terminals other than ground terminals	0.08 to 1.5 mm ² AWG28 to 16	8 to 10 mm	



Conductor length (stripping length)

Dimensions (Unit/mm)

Analog Output Unit NX-DA□□□□ 12 mm Width



Related Manuals

	Cat. No.	Model Manual name		Application	Description	
-	W522	NX-AD NX-DA NX-TS	NX-series Analog I/O Units User's Manual	Learning how to use NX-series Analog I/O Units and Temperature Input Units	The hardware, setup methods, and functions of the NX- series Analog I/O Units and Temperature Input Units are described.	

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

<u>Errors and Omissions.</u> <u>Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is accurate.</u> assumed for clerical, typographical or proofreading errors or omissions.

2013 4

In the interest of product improvement, specifications are subject to change without notice.

