

AGILA LIGHT

1477PAO100P30-11 (10)

EAN 4031582458008



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila light
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	125 mm
Overall weight	0.38 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	28 mm
Swivel radius	87 mm
Swivel interference	174 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Polyurethane, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	25 mm
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm