

CAT. N° 0 784 50



## 3-WIRE MOTION SENSOR MOSAIC - WITH NEUTRAL - IR DETECTION - 400 W- WHITE

|                           |       |
|---------------------------|-------|
| Pack (number of units)    | 1     |
| Volume (dm <sup>3</sup> ) | 0,235 |
| Weight (g)                | 69,00 |

### Product characteristics

#### 3-wire motion sensors, with neutral

##### IR detection - 400 W

- Accepted power by lamp type:
  - LEDs: 0 to 50 W
  - Compact fluorescent: 0 to 50 W
  - LEDs, CFLs, Halogen with ferromagnetic or electronic transformer: 0 to 200 VA
  - fluo tubes with ferromagnetic or electronic transformer: 0 to 150 VA
  - Halogen 230 V, incandescent: 0 to 400 W
- Only one detector per circuit
- No additional remote manual control with push button
- Time delay setting from 10 s to 10 min
- Light level threshold setting from 5 lux to 1275 lux
- Standby consumption: 0.55 W
- White

### General characteristics

#### Mosaic™ Programme mechanisms - motion and presence sensors

- All sensors are compatible with any lamp - Detection field: 120°
- Detection range: 8 m
- Recommended installation height: 1.20 m
- Integrated self-protection against overloads and short-circuits.
- 2 modules

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.880\)](#)
- [Technical page \(p.882\)](#)



#### Installation & technical data

- [F01966EN-04](#)



#### Installation instructions & related documents

- [LE07800AA](#)