


Switches > Push Button Switches

Configuration (Pole-Throw): **Single Pole - Single Throw**Push Button Switch Product Type: **Anti-Vandal Switch**Number of Actuators: **Single**Actuator Profile: **Flush**Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Long Leads
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	Without
Actuator Style	Round Actuator

Configuration Features

Panel Cutout Size	22.2 (Diameter) mm[.87 (Diameter) in]
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Switch Feedback Type	Non-Tactile
Operating Function	1 Pole, NO, Momentary

Electrical Characteristics

Contact Current Rating	1 A
Operating Voltage Range	5 – 24 VDC

Body Features

Case Material	Stainless Steel
Sealing Method	Epoxy
Actuator Material	Steel
Product Orientation	Vertical
Actuator Force	204 – 510 g[7.2 – 18 oz]
Actuator Profile	Flush
Bushing Style	Threaded
Bushing Thread Size	M22 x 1
Actuator Color	Silver

Mechanical Attachment

Attachment Method	Screw-On
-------------------	----------

Housing Features

Low Profile	Yes
-------------	-----

Dimensions

Bushing Length	17 mm[.67 in]
Bushing Diameter	22 mm[.87 in]

Usage Conditions

Operating Temperature Range	-20 – 65 °C[-4 – 149 °F]
-----------------------------	--------------------------

Industry Standards

IP Rating	IP68
-----------	------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (4% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2213772-3
AV22 SPM 3A MOVE RING LED
GREEN 12V




TE Part # 1-2213772-7
AV22 SPM 3A MOVE RING LED BLUE
12V



TE Part # 2213771-1
AV22 SPM 3A NO LED




TE Part # 2213772-5
AV22 SPM 3A MOVE RING LED RED
12V




TE Part # 5-2213772-5
AV22 DPM 3A MOVE RING LED
GREEN 24V

Also in the Series | [ALCOSWITCH AVP22](#)



Anti-Vandal Switches(12)



Push Button Switches(12)

Customers Also Bought



TE Part #K1161759
Emergency Stop Switch ES-2002-T312-020B



TE Part #2342842-4
AVP22M FLAT S16 RGB R 500MM/1X6



TE Part #2342843-1
AVP22M CONC. AIO RGB R 500MM /1X6

Documents

Product Drawings

AVP22M CONC. S16 NL 500MM/1X6

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2342844-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2342844-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2342844-4_A.3d_stp.zip](#)

English

Datasheets & Catalog Pages

AVP Series Anti Vandal Illuminated and Non-Illuminated Piezo Switches

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.