



E2E-X5C118-M1

Proximity sensor, inductive, nickel-brass, short body, M18, shielded, 5 mm, DC, 3-wire, NPN NO, M12 connector

Specifications

Size	M18
Mounting type	Flush
Sensing distance	5 mm
Overall length of sensor	53 mm
Thread length	34 mm
Material housing	Brass, nickel plated
Output type	NPN
Operation mode	NO
Connection method	Connector M12
Cable specifications	-
IO-Link function	✗
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP69K

Accessories



Y92E-J18S30

Mounting Sleeves e-jig for M18 Prox

Related products



M12 Connectors & Cordsets

Industrial connectors & cordsets for any application

Downloads

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q) - Basic Models Index list

EN PDF 7.27 MB



E2E(Q)- XB_XC_basic_model Instruction Sheet

EN PDF 2.28 MB



IO-Link Series Brochure

EN PDF 6.41 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 24 February, 2026. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://www.industrial.omron.eu)