



EN ISO 20345:2011



MODULAR
BELLUNO
83295-07LL

S3 SRC

Size: 41-47 Modular-fit L
Weight: 610 gr.

Working Environment:
Finishing-off building, Logistics
and Light Industry, Components
and Automotive, ESD Areas



FEATURES

UPPER

Drummed leather Hydro 1,8-2,0 mm
Pu Coated Leather
Reflex insert

LINING

3D Air circulation 320 gr.

ANTISLIP LINING DUALMICRO

INSOLE

Blow-fit 2.0

TOE CAP

CTC- Composite Toe Cap

RESISTANCE TO PERFORATION

Zero(K) Perforation resistant

TYPE

Ankle boot

SOLE

PU / PU ESD-PLUS SRC

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

TECHNOLOGIES

Removable Insole

2.0 blow fit

Anatomical and ergonomic removable insole with Flyfit, in direct contact with the foot, transpiring, and comfortable. The E.V.A. HD perforated and thermoformed support ensures comfort and energy absorption



Protection elements

ZERO(k) ANTIPERFORATION



Toecap made of plastic, incredibly light and resistant to impact of over 200J, elastic. Athermic. Not detected by metal detector. Fabric anti-perforation foil. Resistant to over 1100 N with zero perforation.



Lateral stability

dynamic HC control technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



SRC (SRA+SRB)



SOLE 83
PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.47
	HEEL (CONTACT ANGLE 7°) ≥0.28	0.43
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.21
	HEEL (CONTACT ANGLE 7°) ≥0.13	0.16

EN ISO 20344:2011