

ESD SMD tweezers 110 mm form 4 stainless steel, dissipative


Art.-No.	5-049-13
Description	ESD SMD tweezers 110 mm form 4 stainless steel, dissipative
Application	assembly tweezers, SMD/THT, watchmakers tweezers, precision tweezers
Specification	not serrated jaws

Material	stainless steel
Surface/Coating	ESD powder coated
Features	stainless, antimagnetic, acid-resistant, dissipative
Surface resistance	10^6 to 10^9 Ohm

Shape	TG: Tapered tips straight
Icon No.	TG2

Dimensions and weight

A = 30 mm
B = 0.3 mm
C = 0.4 mm
Ai = 10 mm



length 110 mm
weight 15 g

Application and technical data

Tweezers for SMD/THT technology.

Austenitic chromium-nickel stainless steel with low carbon content for good corrosion resistance (not seawater resistant).