



30 and 40 W - 10 Nm - Right-angle gearbox 801410 SNi10 Part number 80141002



- Output perpendicular to motor
- Ideal for short reduction ratios
- Ideal for very compact applications
- Silent operation
- Non-reversible movement at high ratios

	Type	With built-in electronic control	Without built-in control, with Hall effect sensors	Ratios (i)	Output speed (rpm) 24 V DC	Available torque (Nm)	Efficiency (%)
80141001	801410 SNi10	SNi10	-	5	440	0,36	-
80141002	801410 SNi10	SNi10	-	10	220	0,7	-
80141003	801410 SNi10	SNi10	-	20	110	1,5	-
80141004	801410 SNi10	SNi10	-	30	73	1,8	-
80141006	801410 SNi10	SNi10	-	50	44	2,4	-
CONTACT US	801410 SNi10	SNi10	-	5	440	0,416	-
CONTACT US	801410 SNi10	SNi10	-	10	220	0,768	-
CONTACT US	801410 SNi10	SNi10	-	20	110	1,7	-
CONTACT US	801410 SNi10	SNi10	-	30	73	2	-
CONTACT US	801410 SNi10	SNi10	-	50	44	2,7	-
CONTACT US	801410 SNi10	SNi10	-	5	400	0,5	-
CONTACT US	801410 SNi10	SNi10	-	10	200	1	-
CONTACT US	801410 SNi10	SNi10	-	20	100	2,3	-
CONTACT US	801410 SNi10	SNi10	-	30	67	2,6	-
CONTACT US	801410 SNi10	SNi10	-	50	40	3,6	-
CONTACT US	801410 TNi20	TNi20	-	5	440	0,6	-
CONTACT US	801410 TNi20	TNi20	-	10	220	1,0	-
CONTACT US	801410 TNi20	TNi20	-	20	110	1,7	-
CONTACT US	801410 TNi20	TNi20	-	30	73	2,1	-
CONTACT US	801410 TNi20	TNi20	-	50	44	2,4	-
MADE TO ORDER	801410 TNi20	TNi20	-	5	440	0,416	-
MADE TO ORDER	801410 TNi20	TNi20	-	10	220	0,768	-
MADE TO ORDER	801410 TNi20	TNi20	-	20	110	1,7	-
MADE TO ORDER	801410 TNi20	TNi20	-	30	73	2	-
MADE TO ORDER	801410 TNi20	TNi20	-	50	44	2,7	-
CONTACT US	801410 TNi20	TNi20	-	5	400	0,5	-
CONTACT US	801410 TNi20	TNi20	-	10	200	1	-
CONTACT US	801410 TNi20	TNi20	-	20	100	2,3	-
CONTACT US	801410 TNi20	TNi20	-	30	67	2,6	-
CONTACT US	801410 TNi20	TNi20	-	50	40	3,6	-
CONTACT US	801415	-	yes	5	440	0,6	80
CONTACT US	801415	-	yes	10	220	1,0	70
CONTACT US	801415	-	yes	20	110	1,7	61

CONTACT US	801415	-	yes	30	73	2,1	49
CONTACT US	801415	-	yes	50	44	2,4	28
CONTACT US	801415	-	yes	5	440	0,416	
CONTACT US	801415	-	yes	10	220	0,768	
CONTACT US	801415	-	yes	20	110	1,7	
CONTACT US	801415	-	yes	30	73	2	
CONTACT US	801415	-	yes	50	44	2,7	
MADE TO ORDER	801415	-	yes	5	400	0,5	
MADE TO ORDER	801415	-	yes	10	200	1	
MADE TO ORDER	801415	-	yes	20	100	2,3	
MADE TO ORDER	801415	-	yes	30	67	2,6	
MADE TO ORDER	801415	-	yes	50	40	3,6	

Motor	80140004
Gearbox	81041
Nominal motor power at 24 V (W)	32
Max. torque (Nm)	10
Axial load dynamic (N)	10
Radial load dynamic (N)	15
Temperature rise at 50% cycle (°C)	45
Weight (g)	1500
Protection index	IP54

N°	Legend
1	4 x M5 depth 8 mm (on rectangle 30x50)
2	Length of cable 400 ± 10 mm
3	4 x M4 over Ø 36 depth 8 mm
4	4 x M5 over depth 8 mm (on rectangle 30x50)

The left-hand and right-hand sides of the gearbox are identical

- Other powers (60 W - 95 W)
- Dimensions of gearbox shaft
- Without cable but with connector integrated in motor
- Cable length, with or without connector
- Other reduction ratios
- Mechanical holding brake

The limits and precautions for use described in the 80140 brushless motor section must be observed.

The limits and precautions for use described in the 80140 brushless motor section must be observed.