



Part Number : [1300100497](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 23.0m (9.84') Length

Series Number : 130010

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 113030K13M230



Documents & Resources

Drawings

[1300100497_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 3 Poles, Male (Straight) to Female (Straight), 16 AWG, Yellow TPE Cable, 23.0m (9.84') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	78678884071

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.28mm (.405")
Cable Length	23.0m (75.46')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change

Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1527.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16