

ClimaSys forced vent. IP54, 300m3/ h, 48V DC, with outlet grille and filter G2

NSYCVF300M48DPF

EAN Code: 3606480151316

Price: 190,10 EUR

Main

Range	ClimaSys	
product name	ClimaSys CV	
Product or component type	Fan	
Type of filter	Standard	
Flow rate	Free flow rate with standard filter: 262 m3/h	
[Us] rated supply voltage	2560 V	
Input voltage	48 V DC	

Complementary

Absorbed power	11 W	
[In] rated current	0.24 A	
Noise level < at	5556 dB	
Bearing type	Ball	
Height	External: 268 mm	
Width	External: 248 mm	
Depth	External : 103.4 mm	
Cut-out dimensions	223 x 223 mm	
Net weight	1.1 kg	
Material	Outlet grille: injected thermoplastic (ASA PC)	
Colour	Outlet grille: grey (RAL 7035)	
Ambient air temperature for operation	-1070 °C	
Ambient air temperature for storage	-4070 °C	
Maximum pressure	158 Pa flow rate 0 m³/h	
Connections - terminals	Cable	
IP degree of protection	IP54	
Device composition	axial motor protective grille: on the front and rear surfaces filter: front of axial motor	

Rates duty January 2016

1 outlet grille: front 1 cut-out template 1 power cord Condition of use Surrounding environment must be relatively clean

Filter must be cleaned and replaced regularly

Flow rates depends on the work point, see ProClima software Outside temperature must be 5 °C lower than inside temperature

Overfrequent filter replacement should be avoided

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	25.000 cm
Package 1 Length	28.000 cm
Package 1 Weight	1.360 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	50
Package 2 Height	100.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	83.000 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	61d9d3f3-5a49-48f8-8056-1a5ad0ad4c76

Use Again

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Take-back	No	