




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	2
Number of Loaded Positions	2
Number of Power Positions	2
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	2



Number of Rows	1
----------------	---

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------

Body Features

Connector & Keying Code	A
Primary Product Color	Blue

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.8 – 3 µm[31.496 – 118.11 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Mating Tab Width	1.5 mm[.059 in]
PCB Contact Termination Area Plating Material Thickness	1 µm[39.36 µin]
Contact Shape & Form	Rectangular
Contact Layout	Inline
Contact Mating Area Length	6 mm[.236 in]
Contact Base Material	Copper Alloy
Mating Tab Thickness	.5 mm[.02 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	10 A

Termination Features

Rectangular Termination Post & Tail Width	1.1 mm[.043 in]
Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Termination Post & Tail Length	3.7 mm[.146 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Window
Mating Retention	With



Mating Alignment Type	Keyed
PCB Mount Retention Type	Kinked
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Mating Entry Location	Top
Housing Material	Nylon 6/6 GF
Centerline (Pitch)	7.92 mm [.312 in]

Dimensions

Connector Width	11.75 mm [.462 in]
PCB Thickness (Recommended)	1.6 mm [.063 in]
Connector Height	14.5 mm [.57 in]
Connector Length	14.97 mm [.589 in]

Usage Conditions

Operating Temperature (Max)	105 °C [221 °F]
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	250
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant







China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-1747052-4 GIC7.92 2POS_HDR ASS'Y YELLOW KEYING B	 TE Part # 1747052-2 GIC7.92 2POS_HEADER ASS'Y RED KEYING A	 TE Part # 2-1747052-2 GIC7.92 2POS_HDR ASS'Y RED KEYING C	 TE Part # 1747052-5 GRACE INERTIA CONNECTOR 7.92 2POS HEADER
 TE Part # 3-1747052-3 GIC7.92 2POS_HDR ASS'Y BLUE KEYING D	 TE Part # 1747052-4 GIC7.92 2POS_HEADER ASS'Y YELLO KEYING A	 TE Part # 2-1747052-4 GIC7.92 2POS_HDR ASS'Y YELLOW KEYING C	 TE Part # 1-2232784-1 GIC7.92 2POS_HEADER ASS'Y NAT KEYING B




TE Part # 3-1747052-2
GIC7.92 2POS_HDR ASS'Y RED
KEYING D



TE Part # 3-1747052-5
GIC7.92 2POS_HDR ASS'Y GREEN
KEYING D



TE Part # 1-1747052-3
GIC7.92 2POS_HEADER ASS'Y BLUE
KEYING B



TE Part # 1-1747052-5
GIC7.92 2POS_HDR ASS'Y GREEN
KEYING B



TE Part # 2-1747052-5
GIC7.92 2POS_HDR ASS'Y GREEN
KEYING C



TE Part # 1-1747052-1
GIC7.92 2POS_HEADER ASS'Y NAT
KEYING B




TE Part # 2-1747052-1
GIC7.92 2POS_HDR ASS'Y NAT
KEYING C



TE Part # 1-2232784-2
GIC 7.92MM CONN HDR ASS'Y 2POS
RED

Also in the Series | GRACE INERTIA 7.92




PCB Headers & Receptacles(21)




Rectangular Connector Housings(18)



Rectangular Power Connectors(39)



Standard Rectangular Connectors(18)




Wire-to-Board Headers & Receptacles
(21)


Customers Also Bought



TE Part #179844-1
AMP POWER D/LOCK T/HDR ASSY 2P




TE Part #917780-1
2.5 S.D.L POST HDR ASY 2P STD



TE Part #2-2360547-2
SGI 1.5 HDR, 2P, VT, Key B, Black



TE Part #2-2360545-8
SGI 1.5 HDR, 8P, RA, Key B, Black



TE Part #796642-2
2POS 5.0MM CE VRT HDR,TRM BLK



TE Part #2-2360545-3
SGI 1.5 HDR, 3P, RA, Key B, Black



TE Part #2-2360547-3
SGI 1.5 HDR, 3P, VT, Key B, Black



TE Part #5-1376492-2
2.5 SMC HDR 2P WHITE TAPE



TE Part #1747052-1
GRACE INERTIA CONNECTOR 7.92
2POS_HEADER



TE Part #1747052-5
GRACE INERTIA CONNECTOR 7.92
2POS_HEADER

Documents

Product Drawings

GIC7.92 2POS_HEADER ASSY BLUE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1747052-3_F.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1747052-3_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1747052-3_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English