

## General Information

<b>Extended Product Type:</b>	A42 112-100
<b>Product ID:</b>	2CMA170510R1000
<b>ABB Type Designation:</b>	A42 112-100
<b>EAN:</b>	7392696705103
<b>Catalog Description:</b>	Active energy Cl. B;
<b>Long Description:</b>	Electricity meter, 1 phase, Active energy Cl. 1 & B, Approved according to: IEC 62052-11, IEC 62053-21, EN 50470-1, EN 50470-3

## Additional Information

<b>ABB Type Designation:</b>	A42 112-100
<b>Accuracy:</b>	Active energy Cl. B
<b>Communication:</b>	Modbus RTU / EQ bus
<b>Communication Interface:</b>	Pulse output
<b>Connecting Capacity Main Circuit:</b>	0.5 ... 10 mm <sup>2</sup>
<b>Country of Origin:</b>	Sweden (SE)
<b>Customs Tariff Number:</b>	90283011
<b>Data Sheet, Technical Information:</b>	2CMC480001C0201
<b>Declaration of Conformity - CE:</b>	2CMC484002D0001
<b>Degree of Protection:</b>	IP20
<b>E-number:</b>	0980692
<b>EAN:</b>	7392696705103
<b>ETIM 4:</b>	EC001506 - Electronic kilowatt-hour meter
<b>ETIM 5:</b>	EC001506 - Kilowatt-hour meter
<b>ETIM 6:</b>	EC001506 - Kilowatt-hour meter
<b>Enclosure Material:</b>	Plastic
<b>Environmental Information:</b>	2CMC484005D0001
<b>Frequency (f):</b>	50/60 Hz
<b>Function:</b>	Electricity meter
<b>Gross Weight:</b>	0.279 kg
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Instructions and Manuals:</b>	2CMC484004M0201
<b>Invoice Description:</b>	kWh meter#A42 112-100
<b>Meter Type:</b>	Transformer connected
<b>Minimum Order Quantity:</b>	1 piece
<b>Mounting Type:</b>	DIN rail
<b>Number of Phases:</b>	1
<b>Object Classification Code:</b>	P
<b>Package Level 1 EAN:</b>	7392696705103
<b>Package Level 1 Gross Weight:</b>	0.279 kg
<b>Package Level 1 Height:</b>	68 mm
<b>Package Level 1 Length:</b>	94 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	100 mm
<b>Product Main Type:</b>	A42
<b>Product Name:</b>	Electricity Meter

<b>Product Net Depth:</b>	65 mm
<b>Product Net Height:</b>	97 mm
<b>Product Net Weight:</b>	0.207 kg
<b>Product Net Width:</b>	70 mm
<b>Rated Current (I<sub>n</sub>):</b>	6 A
<b>Rated Voltage (U<sub>r</sub>):</b>	57 ... 288 V
<b>RoHS Date:</b>	2011-44
<b>RoHS Information:</b>	2CMC484006
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Electricity meter A42 112-100
<b>Size:</b>	97X70X65
<b>Standards:</b>	EN 50470-1
<b>Sub-Function:</b>	Steel

