




Datasheet

RS Tachometer

Stock Number: 229-6483

ENGLISH



FEATURES

- * World's patent, Multi-functions, one instrument combine Photo Tachometer RPM) and Contact Tachometer (RPM, m/min., ft/min.).
- * Wide measuring range : 0.5 to 100,000 RPM.
- * < 1,000 RPM, 0.1 RPM resolution .
- * High precision with 0.05% accuracy.
- * Memorize the last value, max., value, min. value
- * High visible LCD display.
- * Exclusive one chip LSI circuit & crystal time base
- * The use of durable, long lasting components, including a strong, light weight ABS plastic housing, assures almost maintenance free performance for many years.



FEATURES

* World's patent, Multi-functions, one instrument combine Photo Tach.(RPM) & Contact Tach. (RPM, m/min., ft/min.).	* High visible LCD display gives RPM reading exactly with no guessing or errors & saves battery energy.
* Wide measuring range from 0.5 to 100,000 RPM.	* This tachometer used the exclusive one chip MICRO-COMPUTER LSI circuit & crystal time base, offer the high accurate measurement & fast sampling time.
* 0.1 RPM resolution for the measured value < 1000 RPM.	* The use of durable, long lasting components, including a strong, light weight ABS plastic housing, assures almost maintenance free performance for many years.
* High precision with 0.05% accuracy.	* The housing cabinet has been carefully shaped to fit comfortable in either hand.
* The last value, max., value, min. value will be stored into the memory automatically & can be obtained by pressing MEMORY CALL BUTTON.	

SPECIFICATIONS

Measurement & Range	<i>Photo Tachometer :</i> 5 to 99,999 RPM.	Operating Humidity	Less than 80% R.H.
	<i>Contact Tachometer :</i> 0.5 to 19,999 RPM.	Memory	Last/Max./Min. value.
	<i>Surface Speed :</i> m/min. - 0.05 to 1,999.9 m/min. ft/min. - 0.2 to 6,560 ft/min.	Battery	4 x 1.5V AA (UM-3) batteries.
Resolution	<i>RPM:</i> 0.1 RPM (< 1,000 RPM). 1 RPM (1,000 RPM).	Power Consumption	<i>Photo type :</i> Approx. DC 153 mA.
	<i>m/min.:</i> 0.01m/min. (< 100 m/min.). 0.1m/min. (100 m/min.).		<i>Contact type :</i> Approx. DC 10 mA.
	<i>ft/min.:</i> 0.1 ft/min. (< 1,000 ft/min.). 1 ft/min. (1,000 ft/min.).	Size	195 x 61 x 38.5 mm. (7.6 x 2.4 x 1.5 inch).
Display	5 digits, 10 mm (0.4") LCD.	Weight	280g (0.61 LB) * including batteries.
Accuracy	± (0.05% + 1 digit).	Accessories Included	Carrying case..... 1 PC.
Time base	Quartz crystal.		Reflecting tape marks (600 mm)..... 1 PC.
Circuit	Exclusive one-chip of microcomputer LSI circuit.		RPM adapter (CONE) 1 PC.
Operating Temperature	0 - 50 °C (32 - 122 °F).		RPM adapter (FUNEL) 1 PC.
Patent		<i>The DT-2236 had following countries patent & patent pending :</i> USA - 4,823,080 GERMANY - G9015492.4, G8708922.0 TAIWAN - 45478 & other countries patent pending.	