

## **ESD SMD tweezers ULTRA FINE** 110 mm form 3c stainless steel,thin straight-pointed, dissipative

5-072-UF-13 Art.-No.

**Description** ESD SMD tweezers ULTRA FINE 110 mm form 3c stainless steel,thin straight-pointed, dissipative

**Application** Electronics, SMD/THT assembly, precision mechanics, robotics, watchmakers, jewelers, medical

technology, precision work

**Specification** not serrated jaws, tip tolerance +/-0.05

**Material** stainless steel

Surface/Coating ESD powder coated

**Features** stainless, antimagnetic, acid-resistant, dissipative


10^6 to 10^9 Ohm Surface resistance

Shape NG: Normal tips straight

Icon No. NG1

## **Dimensions and weight**

A = 46 mmB = 0.1 mmC = 0.2 mm





Phone: 00 49 (0) 2191 96 50-0

www.bernstein-tools.de

length 110 mm weight 11 g

## Application and technical data

For precise gripping, holding, and positioning work in laboratories, on testing equipment, especially under the microscope. With a tip dimension of 0.2 mm with a tolerance of +/-0.05, also suitable for equipping robotics (pick-and-place), allows repeatable adjustment.

100% stainless steel anti-magnetic, rust and acid resistant, non-reflective matt fine polished. Stainless austenitic chromium nickel quality steel with low carbon content, for good corrosion resistance (not seawater resistant). Dissipative black ESD coating achieves a surface leakage resistance of 10^6 to 10^9 ohm.