



RAYCHEM INSTALITE LIGHTWEIGHT BRAID

UP TO 50% LIGHTER THAN TRADITIONAL COPPER BRAID—WITH
EXCELLENT EMI PERFORMANCE AND LIGHTNING PROTECTION

WEIGHT SAVINGS

- Up to 50% lighter than traditional braid

COST EFFECTIVE

- Easy transition from traditional braids

EXCELLENT SHIELDING

- Covers wide frequency range
- Better low-frequency performance than plated fibers or microfilaments
- Lightning protection

EASY TO USE

- Uses existing termination tooling and processes

Less Weight in Familiar Braid Technology

Offering up to 50% weight savings over traditional copper braids, INSTALITE lightweight braid has excellent electrical shielding performance over a wide frequency range. Made from a high-performance nickel-plated copper alloy, the RoHS-compliant pull-on braid is supplied on a former for easy installation onto various substrates.

Available in diameters from 3 to 20 mm, INSTALITE braid is more flexible than traditional metal braids, making it very user friendly to work with.

Low Risk Alternative for Lightweight Shielding

Since INSTALITE braid uses well-established metal braiding, the transition from traditional braids to INSTALITE braid is easy. The product can be terminated by standard tooling and installation procedures for existing backshells and band straps, making it easy to introduce it into current applications.

RAYCHEM INSTALITE LIGHTWEIGHT BRAID

EMI and Lightning Protection That Is Up to 50% Lighter



APPLICATIONS

- Military Harnesses
- Commercial Aerospace
- Unmanned Vehicles
- Space

MATERIALS

- **Braid:** Copper alloy, tin or nickel plated
- **Former:** Plastic

ELECTRICAL

- **Lightning Test:** Waveform 5B, 21 kA


ENVIRONMENTAL

- **Temperature Range:**
Tin Plated (LWB-101-xx): -65°C to +150°C
Nickel Plated: (LWB-103-xx): -65°C to +200°C
- **Salt Spray:** ASTM B117
- **Flex Endurance:** 1000 cycles min., SAE AS4373 method 704 (180-degree bend)
- **RoHS Compliant**
- **Product Specification:** WSD2516
- **Packaging:** 50 and 100-meter spools

Diameter, mm (Inch)	Part Number	
	Tin Plated	Nickel Plated
3 (0.12)	LWB-101-3.0	LWB-103-3.0
6 (0.24)	LWB-101-6.0	LWB-103-6.0
10 (0.40)	LWB-101-10.0	LWB-103-10.0
20 (0.79)	LWB-101-20.0	LWB-103-20.0

INSTALITE Lightweight Braid versus Standard Braid (10 mm Braid)

(Nominal Values)	INSTALITE LWB	Standard Braid
DC Resistance (mΩ/m)	9	3.5
Strand Tensile Strength (N/mm ²)	758	220
Strand Break Strength (N)	15.2	11.14
Weight (kg/km)	28	60



Braids are 10-mm OD

RAY-103 = Traditional braid (control)

LWB-103 lightweight braid = 50% weight savings

Plated fibers = 80% weight savings; 100x worse surface transfer impedance up to 10 MHz

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | Agastat | CII | Hartman | Kilovac | Microdot | Nanonics | Polamco | Raychem | Rochester | DEUTSCH
SEACON Phoenix | L.L. Rowe | Phoenix Optix | SEACON

Get your product to market faster with a smarter, better solution.

te.com/lightweightbraid

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved.
1-1773856-7 ADM/RRD 2.5M 06/2015

INSTALITE, Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other product or company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

North America +1 800 522 6752 • Asia Pacific +86 0 400 820 6015 • France +33 1 34 20 86 86 • Germany +49 6251 133 1999 • United Kingdom +44 800 267 666
Visit te.com for additional country contacts.