

SAFETY DATA SHEET ANTI STATIC SPRAY 569-284-0001

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name ANTI STATIC SPRAY 569-284-0001
Product No. 000162069253

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses As product description

1.3. Details of the supplier of the safety data sheet

Supplier R S Components Limited
Birchington Road
Corby
Northants
NN17 9RS
+44(0)1536 402888 (8am-8pm)
+44(0)1536 401588
technical.help@rs-components.com

1.4. Emergency telephone number +44(0)1536 402888 (8am-8pm)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards Flam. Aerosol 1 - H222
Human health Not classified.
Environment Not classified.

Classification (1999/45/EEC)

F+;R12.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Detergent Labelling:

< 5% non-ionic surfactants
perfumes
Contains NATRIUMNITRIET,d-LIMONENE,SODIUM BENZOATE

Label In Accordance With (EC) No. 1272/2008



Signal Word Danger

Hazard Statements

H222 Extremely flammable aerosol.

Precautionary Statements

P102 Keep out of reach of children.
P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P261 Avoid breathing vapour/spray.
P280 Wear protective gloves.
P305+351+338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+313 If eye irritation persists: Get medical advice/attention.
P501 Dispose of contents/container in accordance with local regulations.

ANTI STATIC SPRAY 569-284-0001

Supplementary Precautionary Statements

P211
P251
P410+412

Do not spray on an open flame or other ignition source.
Pressurized container: Do not pierce or burn, even after use.
Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.

Supplemental label information

H229 Pressurised container: May burst if heated

2.3. Other hazards

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

BUTANE	1-5%
CAS-No.: 106-97-8	EC No.: 203-448-7
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
DIETHANOLAMINE	< 1%
CAS-No.: 111-42-2	EC No.: 203-868-0
Classification (EC 1272/2008) Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT RE 2 - H373	Classification (67/548/EEC) Xn;R22,R48/22 Xi;R38,R41
ISOBUTANE	1-5%
CAS-No.: 75-28-5	EC No.: 200-857-2
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
PROPAN-2-OL	5-10%
CAS-No.: 67-63-0	EC No.: 200-661-7
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R67
PROPANE	5-10%
CAS-No.: 74-98-6	EC No.: 200-827-9
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12

ANTI STATIC SPRAY 569-284-0001

SODIUM NITRITE		< 1%
CAS-No.: 7632-00-0	EC No.: 231-555-9	
Classification (EC 1272/2008)	Classification (67/548/EEC)	
Ox. Sol. 3 - H272	O;R8	
Acute Tox. 3 - H301	T;R25	
Aquatic Acute 1 - H400	N;R50	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General information

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Inhalation

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

5.2. Special hazards arising from the substance or mixture

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

6.2. Environmental precautions

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

6.4. Reference to other sections

SECTION 7: HANDLING AND STORAGE

ANTI STATIC SPRAY 569-284-0001

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

7.3. Specific end use(s)

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTANE	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³	
DIETHANOLAMINE	OES	3 ppm	13 mg/m ³			
PROPAN-2-OL	WEL	400 ppm	999 mg/m ³	500 ppm	1250 mg/m ³	
PROPANE		Asphyxiating	Asphyxiating.	Asphyxiating	Asphyxiating.	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Engineering measures

Provide adequate general and local exhaust ventilation.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

Hand protection

Use protective gloves.

Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	White.
Odour	Characteristic.
Solubility	Soluble in water.
Flammability Limit - Lower(%)	0.8
Flammability Limit - Upper(%)	12.0

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

10.5. Incompatible materials

10.6. Hazardous decomposition products

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

Skin contact

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema.

Eye contact

Irritating to eyes. May cause chemical eye burns.

Route of entry

Inhalation. Skin and/or eye contact.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Dangerous for the environment if discharged into watercourses.

12.1. Toxicity

12.2. Persistence and degradability

Degradability

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

ANTI STATIC SPRAY 569-284-0001

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

14.2. UN proper shipping name

Proper Shipping Name	AEROSOLS
----------------------	----------

14.3. Transport hazard class(es)

ADR/RID/ADN Class	2
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1
IMDG Class	2.1
ICAO Class/Division	2.1
Transport Labels	



14.4. Packing group

ADR/RID/ADN Packing group	N/A
IMDG Packing group	Not Applicable
ICAO Packing group	N/A

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS	F-D, S-U
-----	----------

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Uk Regulatory References

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

Statutory Instruments

Control of Substances Hazardous to Health.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716).

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

ANTI STATIC SPRAY 569-284-0001

Guidance Notes

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

15.2. Chemical Safety Assessment

SECTION 16: OTHER INFORMATION

Revision Date	13/04/2016
Revision	15
Supersedes date	27/10/2015
Risk Phrases In Full	
R8	Contact with combustible material may cause fire.
R12	Extremely flammable.
R22	Harmful if swallowed.
R48/22	Harmful: danger of serious damage to health by prolonged exposure if swallowed.
R11	Highly flammable
R36	Irritating to eyes.
R38	Irritating to skin.
R41	Risk of serious damage to eyes.
R25	Toxic if swallowed.
R67	Vapours may cause drowsiness and dizziness.
R50	Very toxic to aquatic organisms.
Hazard Statements In Full	
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H315	Causes skin irritation.
H222	Extremely flammable aerosol.
H220	Extremely flammable gas.
H302	Harmful if swallowed.
H225	Highly flammable liquid and vapour.
H373	May cause damage to organs <<Organs>> through prolonged or repeated exposure.
H336	May cause drowsiness or dizziness.
H272	May intensify fire; oxidiser.
H301	Toxic if swallowed.
H400	Very toxic to aquatic life.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.