


# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker, Sheet, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, BLUEMARK E.CARD, cable diameter range: 0.6 ... 22 mm, mounting type: insert, Number of individual labels: 24, text field height: 4 mm, text field width: 18 mm

## Your advantages

- The UC-WMT ... UniCard labeling range includes markers for conductor marking with marking collars from the PATG (HF) .../PATG ... system
- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing system
- To simplify mounting, the insert labels are arranged on UniCard sheets so that they can be separated branch by branch
- Labeled insert strips are simply inserted into the collars. This protects the marking against dirt.
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0821085             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BG2217              |
| Product key                          | BG2217              |
| Catalog page                         | Page 202 (C-3-2019) |
| GTIN                                 | 4046356287241       |
| Weight per piece (including packing) | 8.63 g              |
| Weight per piece (excluding packing) | 7.2 g               |
| Customs tariff number                | 39269097            |
| Country of origin                    | PL                  |

# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Conductor marking |
| Type         | Card form         |

### Marking

|                                     |                   |
|-------------------------------------|-------------------|
| Number of individual labels         | 24                |
| Number of individual labels per row | 8                 |
| Identification technology           | UV LED technology |

### Dimensions

|        |        |
|--------|--------|
| Width  | 18 mm  |
| Depth  | 0.7 mm |
| Length | 4 mm   |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 18 mm |
| Text field height | 4 mm  |

### Material specifications

|                                                        |                                |
|--------------------------------------------------------|--------------------------------|
| Color                                                  | red (RAL 3001)                 |
| Material                                               | PA                             |
| Flammability rating according to UL 94                 | V2                             |
| Base element material                                  | PA                             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2                    |
| Components                                             | free from silicone and halogen |

### Cable/line

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 0.6 mm ... 22 mm |
|-------------------------|------------------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Scratch test for the determining scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

## Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

## Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed                                    |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

|               |                                               |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h                                          |

## Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C                                                               |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                         |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |        |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27281106 |
| ECLASS-12.0 | 27281106 |
| ECLASS-13.0 | 27281106 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# UC-WMT (18X4) RD - Conductor marker



0821085

<https://www.phoenixcontact.com/gb/products/0821085>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)