



# TUV T5

## TUV 64T5 HO 4P SE UNP/32

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

### Product data

General Information		Operating and Electrical	
Cap-Base	4PINSSINGLEENDED [ 4 Pins Single Ended]	Power (Nom)	145 W
Remarks	Warnings and Safety: A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner. DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.	Lamp Current (Nom)	0.8 A
Main Application	Disinfection	Voltage (Nom)	175 V
Useful Life (Nom)	9000 h	<b>Mechanical and Housing</b>	
System Description	High Output	Cap-Base Information	4 Pins Single Ended
<b>Light Technical</b>		<b>Approval and Application</b>	
Color Code	TUV	Mercury (Hg) Content (Nom)	5.5 mg
Color Designation	- [ Not Specified]	<b>UV</b>	
Depreciation at Useful Lifetime	15 %	UV-C Radiation at 100 hr	48 W
<b>Product Data</b>		<b>Product Data</b>	
		Full product code	871150026131199
		Order product name	TUV 64T5 HO 4P SE UNP/32
		EAN/UPC - Product	8711500261311
		Order code	927971104099
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	32

# TUV T5

Material Nr. (12NC)	927971104099
Net Weight (Piece)	156.000 g

## Warnings and Safety

## Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 64T5 HO 4P SE UNP/32	19.3 mm	1564.5 mm	1555.2 mm

TUV 64T5 HO 4P SE

## Photometric data

