

PRODUCT-DETAILS

TY528MR-NDT

TYRAP DETECTABLE BLUE 222N



General Information

Extended Product Type	TY528MR-NDT
Product ID	7TCG009330R0025
EAN	5415022507010
Catalog Description	TYRAP DETECTABLE BLUE 222N
Long Description	Detectable Cable Tie, Bright Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 361mm (14.2 Inches), Width of 4.8mm (0.189 Inch), Thickness of 1.3mm (0.05 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds)

Ordering

E-Number (Finland)	1381541
EAN	5415022507010
UPC	786210334615

Dimensions

Product Net Width	0.189 in 4.8 mm
Product Net Depth / Length	14.2 in 341 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	4.32 in 110 mm
Package Level 1 Height	0.78 in 20 mm
Package Level 1 Depth / Length	18.86 in 479 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	10.21 in 259 mm
Package Level 2 Height	14.14 in 359 mm
Package Level 2 Depth / Length	19.65 in 499 mm

Technical UL/CSA

Flammability According to UL94	HB
--------------------------------	----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	4.8 to 102 mm
Color	Blue
Effective Date	20191119
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Main Type	PERFORMANCE CABLE TIES AND ACCESSORIES
Product Name	OTHER ARTICLES OF PLASTIC
Product Type	Detectable
Special Functions	Detectable by metal detectors, X-ray equipment, or visual detection.
Tensile Strength	50 lb 222 N
Thickness	0.05 in 1.3 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000516
Instructions and Manuals	TY528MR-NDT
REACH Declaration	9AKK107992A3997
RoHS Information	9AKK107991A8364

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

