



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151580-1  
OCEAN\_2.0\_APPLICATOR-S-062F067F-RSM

TE Part # 2151580-2  
OCEAN\_2.0\_APPLICATOR-S-062F067FA-RSA

TE Part # 91338-2  
PRO CRIMPER DIE, .64MM

TE Part # 91338-1  
0.64 MM CONTACT PRO-CRIMPER



TE Part # 2305570-1  
Strip Terminal Cutter-Side Feed-No Crimp

TE Part # 638379-3  
.64MM 2X4 CAP ASSY, KEY C

TE Part # 1438726-2  
70 Way Inline Sealed Hybrid Cap Assy

KIT  
TE Part # 7-2151580-7  
OCEAN\_2.0\_SPARE\_PART\_KIT-062F067F

Customers Also Bought

TE Part #1456968-2  
CONTACT,FEMALE, 0.64, 18 AWG, AG

TE Part #6-928918-1  
MQS0,63 Sn tab LL unseal. 0,2-0,35

TE Part #1-174957-1  
070 MLC CAP ASSY V 12P

TE Part #1326029-4  
2.8MM BLADE, UNSEAL,10-12AWG

TE Part #1438136-1  
70 WAY HARNESS ASSY KEYA(PROD)

TE Part #1-1456570-3  
SUB-ASSY,PLUG,2.8/6.3,38 WAY,ABS

TE Part #2-1456570-6  
SUB-ASSY,PLUG,2.8/6.3,38 WAY,ABS

TE Part #1456996-1  
SUB-ASSY,COVER/LEVER,38 WAY,ABS

TE Part #1326942-3  
1 X 6 SEALED MAF CONN ASSY 1&6 blocked

TE Part #184153-1  
2 POS. END CAP HSG., KEY C

Documents

Product Drawings

0.64MM PIN CONTACT, CRIMP, 18-

English

0.64MM PIN CONTACT, CRIMP, 18-

English

CAD Files

Customer View Model

ENG\_CVM\_1488208-1\_O.3d\_igs.zip



English

Customer View Model

[ENG\\_CVM\\_1488208-1\\_O.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1488208-1\\_O.2d\\_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English