

Surge protection plug - PT 2-TELE-ST - 2838733

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Surge protection plug for base element, for protecting a double conductor of analog telecommunication interfaces.



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 044677
Weight per Piece (excluding packing)	29.22 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Height	45 mm
Width	17.7 mm
Depth	52 mm
Horizontal pitch	1 Div.
Complete module height	90 mm
Complete module width	17.7 mm
Complete module depth	65.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA
Inflammability class according to UL 94	V0
Color	black

Surge protection plug - PT 2-TELE-ST - 2838733

Technical data

General

Standards for air and creepage distances	VDE 0110-1
	IEC 60644-1
Mounting type	On base element
Type	DIN rail module, two-section, divisible
Number of positions	2
Direction of action	Line-Line & Line-Earth Ground

Protective circuit

IEC test classification	C1
	C2
	C3
	D1
	B2
VDE requirement class	C1
	C2
	C3
	D1
	B2
Maximum continuous voltage U_C (wire-wire)	185 V DC
	130 V AC
Maximum continuous voltage U_C (wire-ground)	185 V DC
	130 V AC
Nominal current I_N	450 mA (45°C)
Operating effective current I_C at U_C	$\leq 10 \mu A$
Residual current I_{PE}	$\leq 10 \mu A$
Nominal discharge current I_n (8/20) μs (Core-Core)	10 kA
Nominal discharge current I_n (8/20) μs (Core-Earth)	10 kA
Total surge current (8/20) μs	20 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Earth)	18 kA
Nominal pulse current I_{an} (10/700) μs (Core-Core)	100 A
Nominal pulse current I_{an} (10/700) μs (Core-Earth)	100 A
Impulse discharge current (10/350) μs , peak value I_{imp}	1 kA
Output voltage limitation at 1 kV/ μs (Core-Core) spike	$\leq 300 V$
Output voltage limitation at 1 kV/ μs (Core-Earth) spike	$\leq 300 V$
Output voltage limitation at 1 kV/ μs (Core-Core) static	$\leq 300 V$
Output voltage limitation at 1 kV/ μs (Core-Earth) static	$\leq 300 V$
Residual voltage at I_n , (conductor-conductor)	$\leq 160 V$ (C2 - 10 kV / 5 kA)
Residual voltage at I_n , (conductor-ground)	$\leq 200 V$ (C2 - 10 kV / 5 kA)
Voltage protection level U_p (Core-Core)	$\leq 330 V$ (C2 - 10 kV / 5 kA)
	$\leq 300 V$ (C2 - 2 kV/1 kA)
	$\leq 270 V$ (C1 - 1 kV/500 A)

Surge protection plug - PT 2-TELE-ST - 2838733

Technical data

Protective circuit

	≤ 300 V (B2 - 4 kV/100 A)
Response time tA (Core-Core)	≤ 500 ns
Response time tA (Core-Earth)	≤ 500 ns
Input attenuation aE, sym.	typ. 0.4 dB (≤ 5 MHz)
Cut-off frequency fg (3 dB), sym. in 100 Ohm system	typ. 20 MHz
Capacity (Core-Core)	typ. 30 pF (f=1 MHz / VR= 0 V)
Capacity (Core-Earth)	typ. 30 pF (f=1 MHz / VR= 0 V)
Resistance in series	2.2 Ω ±10 %
Surge carrying capacity in acc. with IEC 61643-21 (Core-Core)	B2 (4 kV / 100 A)
	C1 (1 kV / 500 A)
	C2 (10 kV/5 kA)
	C3 (2 kV/25 A)
	D1 (1 kA)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	B2 (4 kV / 100 A)
	C1 (1 kV / 500 A)
	C2 (10 kV/5 kA)
	C3 (2 kV/25 A)
	D1 (1 kA)

Connection data

Connection method	Screw connection (in connection with the base element)
Connection type IN	PLUGTRAB plug-in system
Connection type OUT	PLUGTRAB plug-in system

Standards and Regulations

Standards/regulations	IEC 61643-21
-----------------------	--------------

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943

Surge protection plug - PT 2-TELE-ST - 2838733

Classifications

ETIM

ETIM 5.0	EC000943
----------	----------

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST

Accessories

Accessories

Device marking

Zack marker strip - ZBN 18:UNBEDRUCKT - 2809128



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 18 mm, Lettering field: 18 x 5 mm

Labeled terminal marker

Surge protection plug - PT 2-TELE-ST - 2838733

Accessories

Zack Marker strip, flat - ZBF 5,LGS:FORTL.ZAHLEN - 0808671



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

Zack Marker strip, flat - ZBF 5,LGS:GERADE ZAHLEN - 0810821



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Consecutive numbers 2 - 20, 22 - 40, etc. up to 82 - 100, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

Zack Marker strip, flat - ZBF 5,LGS:UNGERADE ZAHLEN - 0810863



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Odd numbers 1 - 19, 21 - 39, etc. up to 81 - 99, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

Zack Marker strip, flat - ZBF 5,QR:FORTL.ZAHLEN - 0808697



Zack Marker strip, flat, Strip, white, labeled, Printed vertically: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 100, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

Marker pen

Marker pen - X-PEN 0,35 - 0811228



Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm

Terminal marking

Surge protection plug - PT 2-TELE-ST - 2838733

Accessories

Zack Marker strip, flat - ZBF 5:UNBEDRUCKT - 0808642



Zack Marker strip, flat, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.1 x 5.2 mm


Zack Marker strip, flat - ZBF 5/WH-100:UNBEDRUCKT - 0808668



Zack Marker strip, flat, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into flat marker groove, For terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

Drawings

Dimensioned drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram

