

Combi Drill LXT®

DHP482

18V • 62 Nm • 0 – 1 900 min⁻¹

Powerful general-use combi drill with hammer action for professionals

An efficient drill for professional screwdriving and drilling with or without hammer action, two power settings. Max. torque of 62 / 36 Nm. A versatile tool for fitters, builders and maintenance staff. Integrated LED light.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 600 / 1900 min ⁻¹
Max. fastening torque Hard/Soft	62 / 36 Nm
Max Torque	64 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 9000 / 28500 min ⁻¹
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Concrete	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	51 mm
Drilling Capacity Flat bit	38 mm
Drilling Capacity Hole Saw	51 mm
Driving Shank	1/2"-20UNF "

User benefits

- Highly efficient and compact machine for professional use
- Battery protection system automatically shuts off power when the battery level is low
- Optimal handle design
- LED light illuminates the work site
- Ergonomic handle for easy manoeuvring

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing