



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 20800 – 33100 CMA

Stud Size: 1/4, M6

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4, M6
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	20800 – 33100 CMA
Stud Diameter	6.73 mm[.265 in]



Tongue Thickness	.79 mm[.031 in]
Product Length	31.65 mm[1.246 in]
Barrel Inside Diameter	5.89 mm[.232 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Nickel
Compatible With Wire Plating Material	Nickel

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1490413-2
HYP10 SOLIS HD 8AWG NEST



TE Part # 69217
HYP8/10 SOLIS 6AWG DIE SET




TE Part # 1901002-1
INDENTER, SOLISTRAND



TE Part # 48127
HYP8 SOLIS 6-2AWG INDENTER



TE Part # 1490414-2
HYP10 SOLIS HD 6-4AWG INDENTER




TE Part # 1901000-1
NEST #6



TE Part # 48128
HYP8 SOLIS 6AWG NEST

Customers Also Bought



TE Part #173295-000
RT-1145-OX-12-0



TE Part #50831-1
TERMINAL,PIDG PTFE R 22-20 6




TE Part #322320
DG 22-16COM 22-18MIL HT R 1/4



TE Part #CAT-R21-T319
Single Wall RT 1145: Heat Shrink Tubing



TE Part #EM6341-000
R85049/93-04



TE Part #323794
SPLICE,SOLIS PARA HR 16-14



TE Part #461485-000
55A7027-20-6/9-6CS2510

Documents

Product Drawings
SOLISTRAND 6 S-T HR RING 1/4
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1958285-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1958285-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1958285-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English