



FS108P

ProSafe 8 Port 10/100 Switch with 4 Port Power over Ethernet


- *Help is there when you need it! NETGEAR provides 24x7 technical support* in English, with selected local language support during office hours.*

Affordable Power over Ethernet Switching

The ProSafe FS108P provides power and data from a single point, using Power over Ethernet (PoE) over a single Cat-5 cable. The eight Fast Ethernet ports can be used for any 10/100 Mbps link and four of these ports can supply industry-standard IEEE 802.3af power. Advanced auto-sensing algorithm gives power only to 802.3af end devices, so no need to worry about damaging proprietary PoE or non-PoE equipment. In addition, it discontinues the power when PoE devices are disconnected. Easy and reliable, the ProSafe FS108P automatically determines PoE requirements, speed, duplex, and cable type using AutoUplink™.

The affordably priced ProSafe FS108P delivers PoE to any small business network that wants to simplify the installation of wireless access points and IP-based surveillance cameras. These devices are optimally installed on a ceiling or high on a wall, away from most electrical outlets. PoE eliminates the requirement for a dedicated electrical outlet to power these devices. This allows for flexibility in situating devices where AC power is difficult to access and lowers installation costs. Compact and flexible, the ProSafe FS108P is ideal for small business network that want to inexpensively use PoE to deploy wireless access points and IP-based network surveillance cameras.

- Flexible** Choose to plug in up to eight Ethernet or Fast Ethernet devices and mix in up to four 802.3af IP-based devices like wireless access points or IP-based network surveillance cameras. Place these 802.3af-compliant devices where they belong – high up on walls and ceiling for maximum coverage – or anywhere else you need them. Power and data are carried over standard Cat-5 cabling.
- Plug and Play** The standards-based ProSafe FS108P senses and adjusts for network speed and cabling type automatically, for easy integration into your existing 10/100 Ethernet network. For PoE, the switch automatically detects 802.3af-compliant devices, and supplies power as needed. Front panel LEDs keep you informed of switch and PoE status.
- Quiet and Compact** Engineered for compact convenience, it features a 9-inch, durable metal case that is easily positioned on your desktop or a wall, using the included mounting hardware. The fan-less design quietly integrates in your small office environment.
- Great Value** With data switching and Power over Ethernet integrated into one unit, the FS108P saves space, reduces cables and eliminates the requirement for dedicated electrical outlets – lowering installation costs, simplifying installation of PoE-capable devices, and eliminating the need for electricians or extension cords. All in all a great benefit for a modest price.



Technical Specifications

- **Network Ports:**
 - 8 auto speed-sensing 10/100 RJ-45 ports
- **Network Protocol and Standards:**
 - IEEE 802.3i 10BASE-T
 - IEEE 802.3u 100BASE-TX
 - IEEE 802.3x Flow Control
 - IEEE 802.3af DTE Power via MDI
- **Performance Specifications:**
 - **Forwarding modes:** Store-and-forward
 - **Bandwidth:** 1.6 Gbps
 - **Network latency:** Less than 20 μ s for 64-byte frames in store-and-forward mode for 100 Mbps to 100 Mbps transmission
 - **Buffer memory:** 96 KB embedded memory per unit
 - **Address database size:** 1,000 media access control (MAC) addresses per system
 - **Addressing:** 48-bit MAC address
 - **Mean Time Between Failure (MTBF):** 190,000 hours (~ 21 years)
- **Status LEDs:**
 - **System:** Power, PoE Maximum Power
 - **Per Port:** Link, Activity, Speed, PoE Active, PoE Fault
- **Power Supply:**
 - **Total Power Consumption:** 44 W maximum
 - **802.3af Power Consumption:** 32 W maximum (Ports 1 – 4)
 - 48VDC, 0.8A power output; plug is localized to country of sale
- **Physical Specifications:**
 - **Dimensions (H x W x D):** 1.1 x 9.3 x 4.1 in. (27 x 235 x 103 mm)
 - **Weight:** 1.7 lbs. (0.74 kg)
- **Environmental Specifications:**
 - **Operating temperature:** 32 to 104°F (0 to 40° C)
 - **Storage temperature:** 14 to 158°F (-10 to 70°C)
 - **Operating humidity:** 90% maximum relative humidity, non-condensing
 - **Storage humidity:** 95% maximum relative humidity, non-condensing
 - **Operating altitude:** 10,000 ft (3,000 m) maximum
 - **Storage altitude:** 10,000 ft (3,000 m) maximum
- **Electromagnetic Emissions:**
 - CE mark, commercial
 - FCC Part 15 Class B
 - VCCI Class B
 - EN 55022 (CISPR 22), Class B
 - C-Tick
- **Electromagnetic Immunity:**
 - EN 55024
- **Safety:**
 - CE mark, commercial
 - CE/LVD EN60950
- **Warranty:**
 - 5 years for switch
 - 2 years for power supply

Package Contents

- ProSafe 8 Port 10/100 Switch with Power over Ethernet FS108P
- AC Adapter
- Wall-mount kit
- Installation guide
- Warranty/Support Information card

NETGEAR Related Products

- ProSafe 802.11g Wireless Access Point WG302
- ProSafe 802.11g Wireless Access Point WG102
- FA311 NIC 10/100 Low Profile PCI Network Interface Card

NETGEAR®

4500 Great America Parkway
Santa Clara, CA 95054 USA
Phone: 1-888-NETGEAR
E-mail: info@NETGEAR.com
www.NETGEAR.com

©2004 NETGEAR, Inc. NETGEAR®, the Netgear Logo, Auto Uplink, ProSafe, and Everybody's connecting are trademarks or registered trademarks of Netgear, Inc. in the United States and/or other countries. Microsoft, Windows, and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. Other brand and product names are trademarks or registered trademarks of their respective holders. Information is subject to change without notice. All rights reserved.

* Free basic installation support provided for 90 days from date of purchase. Advanced product features and configurations are not included in free basic installation support; optional premium support available.