



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Tin-Lead**
Wire Contact Termination Area Plating Material: **Tin-Lead**
Contact Retention Within Housing: **With**
Contact Size: **Size 16**

Features

Contact Features

Contact Underplating Material	Nickel
Contact Orientation	Straight
Mating Pin Diameter	1.57 mm[.062 in]
Contact Underplating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Contact Type	Socket
Contact Mating Area Plating Material	Tin-Lead
Wire Contact Termination Area Plating Material	Tin-Lead
Contact Retention Within Housing	With
Contact Size	Size 16
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	13 A

Termination Features



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	2.03 – 2.54 mm[.08 – .1 in]
Wire Size	.8 – 2 mm²

Usage Conditions

Operating Temperature Range	-55 – 90 °C[-67 – 194 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (13% in 4690948374) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 200893-2 INSERTION TOOL CONT	 TE Part # 2151101-1 OCEAN_2.0_APPLICATOR-S-090F120O-RSM	 TE Part # 305183 EXTRACT TOOL TYPE 2 20-16	 TE Part # 7-2151101-7 OCEAN_2.0_SPARE_PART_KIT-090F120O
 TE Part # 91519-1 CCII TYPE III+ PIN SKT 18-14 ASSY	 TE Part # 5-2151101-2 OCEAN_2.0_APPLICATOR-S-090F120O-RSA	 TE Part # 5-2151101-1 OCEAN_2.0_APPLICATOR-S-090F120O-RSM	 TE Part # 2151101-2 OCEAN_2.0_APPLICATOR-S-090F120O-RSA
 TE Part # 539972-1 EXTRACTION TOOL	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp		

Also in the Series | AMP Type III+

 Connector Contacts(260)	 Insertion & Extraction Tools(4)	 Power Contacts(260)
--	---	--



Also in the Series | Circular Plastic Connectors Series 1



Circular Power Connectors(211)



Connector Contacts(260)



Power Contacts(260)

Customers Also Bought



TE Part #1062-16-0644
SOC, SF, SIZE 16, 16-20, AU/SN



TE Part #114008-ZZ
EXT TOOL, SIZE 8, 8-10 AWG, N, GRN



TE Part #HDC34-24
DUST CAP, 24SZ, PLG, AL, LANYARD, HD30



TE Part #2292797-3
AS16,PLUG BACKSHELL KIT,ST,02P, NC08



TE Part #CAT-AM7801-CH8172
AMPSEAL 16 Housings



TE Part #2286014-2
TPA, LED, ASSY



TE Part #102308-000
2020D0309-0



TE Part #2350890-1
20POS,HYBRID,SOC HSG ASSY,SLD, COD A



TE Part #HDB36-24-91SE-059
BR AWY PL ASM,MC

Documents

Product Drawings
III+ SKT,18-14,TIN-LEAD,STRIP
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-66358-2_AR.2d_dxf.zip



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-66358-2_AR.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-66358-2_AR.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

Japanese

[Instruction Sheet \(U.S.\)](#)

English