

# 97 61 145 A

## Crimping Pliers for end sleeves (ferrules)



- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4 in the range from 0.25 up to 2.5 mm<sup>2</sup>
- Crimping in marked trapezoidal dies for reliable connections between the sleeve and the conductor
- Vanadium electric steel; forged, oil-hardened



<b>Article No.</b>	97 61 145 A
<b>EAN</b>	4003773072003
<b>Head</b>	polished
<b>Handles</b>	plastic coated
<b>Applications</b>	End Sleeves (ferrules)
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,25 - 2,5
<b>Number of crimping positions</b>	4
<b>AWG</b>	23 - 13
<b>Length mm</b>	145
<b>Net weight g</b>	140

*technical change and errors excepted*

