

1342906

https://www.phoenixcontact.com/in/products/1342906

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, for mounting on a DIN rail, color: light gray (similar RAL 7035), width: 35.2 mm, height: 99 mm, depth: 113.65 mm, incl. 12 PCB connectors, 3-pos., screw connection, for 2. 5 mm², nominal current: 12 A, 320 V, PCB surface: 6800 mm²

Commercial data

Item number	1342906
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	****
Product key	ACHABK
GTIN	4063151657529
Weight per piece (including packing)	186.53 g
Weight per piece (excluding packing)	147.919 g
Customs tariff number	85369010
Country of origin	DE



1342906

https://www.phoenixcontact.com/in/products/1342906

Set consists of

ME MAX 35 3-3 KMGY - Electronics housing

2713696

https://www.phoenixcontact.com/in/products/2713696



DIN rail housing, Complete housing with metal foot catch, tall design, with vents, width: 35.2 mm, height: 99 mm, depth: 113.65 mm, color: light gray (similar RAL 7035), cross connection: DIN rail connector (optional), number of positions cross connector: 5

ME BUS FE CONTACT - Functional ground contact

2278076

https://www.phoenixcontact.com/in/products/2278076



DIN rail housing, FE contact, width: 5 mm, height: 15.25 mm, depth: 9.5 mm



1342906

https://www.phoenixcontact.com/in/products/1342906

MSTBO 2,5/ 3-G1L KMGY - PCB header

2853750

https://www.phoenixcontact.com/in/products/2853750



PCB headers, nominal cross section: 2.5 mm², color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTBO 2,5/..-G1L, pitch: 5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, plug-in system: COMBICON MSTB 2,5, Pin connector pattern alignment: Orthogonal, locking: without, type of packaging: packed in cardboard, Product with pin output on left side

MSTBO 2,5/ 3-G1R KMGY - PCB header

2853763

https://www.phoenixcontact.com/in/products/2853763



PCB headers, nominal cross section: 2.5 mm², color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTBO 2,5/..-G1R, pitch: 5 mm, connection method: pluggable, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, plug-in system: COMBICON MSTB 2,5, Pin connector pattern alignment: Orthogonal, locking: without, type of packaging: packed in cardboard, Product with pin output on right side



1342906

https://www.phoenixcontact.com/in/products/1342906

MSTBT 2,5 HC/ 3-STP GY7035 - PCB connector

2200333

https://www.phoenixcontact.com/in/products/2200333



PCB connector, nominal cross section: 2.5 mm², color: light gray, nominal current: 16 A (see derating curve), rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTBT 2,5 HC/..-STP, pitch: 5 mm, connection method: Screw connection with tension sleeve, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plugin system: COMBICON MSTB 2,5 HC, locking: without, mounting method: without, type of packaging: packed in cardboard



1342906

https://www.phoenixcontact.com/in/products/1342906

Technical data

Notes

Assembly note	Please observe the assembly instructions available in the download area.
Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)
General	The PCB surface specification is for orientation purposes and is based on a basic PCB. The housing can also accommodate several PCBs.

Product properties

Product type	Stackable housing set
Housing type	DIN rail housing
Housing series	ME-MAX
Number of positions	36
Max. number of positions	36 (pitch: 5 mm)
Number of rows	3
Туре	for mounting on a DIN rail
	incl. 12 PCB connectors, 3-pos., screw connection, for 2.5 mm², nominal current: 12 A, 320 V
Ventilation openings present	yes

Connection data

Connection method	Screw connection with tension sleeve
-------------------	--------------------------------------

Dimensions

Dimensional drawing	h
Width	35.2 mm
Height	99 mm
Depth	113.65 mm
Depth from top edge of DIN rail	107 mm
CB design	
PCB thickness	1.4 mm 1.8 mm

Material specifications

Color (Housing)	light gray (RAL 7035)	
Color (Flousing)	light gray (IVAL 7000)	



1342906

https://www.phoenixcontact.com/in/products/1342906

Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C 55 °C
Ambient temperature (assembly)	-5 °C 100 °C
Relative humidity (storage/transport)	80 % (maximum)

PCB data

Number of PCB holders	2
Type of PCB mount	Latching
Total PCB surface	6800 mm²
Thickness of the PCB	1.4 mm 1.8 mm

Mounting

Mounting type	DIN rail mounting

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton




1342906

https://www.phoenixcontact.com/in/products/1342906

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.



1342906

https://www.phoenixcontact.com/in/products/1342906

Classifications

ETIM 9.0

ECLASS

	ECLASS-11.0	27182702
	ECLASS-13.0	27190301
ET	ТІМ	

EC001031



1342906

https://www.phoenixcontact.com/in/products/1342906

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT (I) Pvt. Ltd. A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420 info@phoenixcontact.co.in