



Klenzeen Hard Surface Wipes

SD0811 v1.0 RS 481-648

Revision 0

Revision date 2011-09-01

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	Klenzeen Hard Surface Wipes
--------------	-----------------------------

1.2. Relevant identified uses of the substance or mixture and uses advised against

Description	Non woven fabric impregnated with a colourless solution.
-------------	--

1.3. Details of the supplier of the safety data sheet

Company	Whitminster International Limited
Address	Unit 3, Tollgate Drive, Tollgate Industrial Estate, Stafford ST16 3HS
Web	www.whitminster.co.uk
Telephone	01785 252760
Fax	01785 251299
Email	julian@whitminster.co.uk
Email address of the competent person	lisa@whitminster.co.uk
Local Supplier	
Company	Klenzeen Ltd
Address	Dudbridge Road Stroud Gloucestershire GL5 3HF United Kingdom
Web	www.klenzeen.co.uk
Telephone	01453 762266
Fax	01453 762277
Email	dave@whitminster.co.uk
Email address of the competent person	lisa@whitminster.co.uk

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: +44 (0) 1536 402888 (8am to 8pm)
Email: technical.help@rs-components.com

1.4. Emergency telephone number

Emergency telephone number	01785 252760
Company	Lisa Frost 08.00 - 18.00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Main hazards	No Significant Hazard
--------------	-----------------------

SECTION 3: Composition/information on ingredients

Klenzeen Hard Surface Wipes

SD0811 v1.0 RS 481-648

Revision 0

Revision date 2011-09-01

3.2. Mixtures

67/548/EEC / 1999/45/EC

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Propan-2-ol	603-117-00-0	67-63-0	200-661-7		10 - 20%	F; R11 Xi; R36 R67
Alkyl(C12-16)dimethylbenzylamm onium chloride		68424-85-1	270-325-2		0.5 - 1%	C; R34 Xn; R21/22 N; R50

SECTION 4: First aid measures

4.1. Description of first aid measures

Eye contact	If the impregnating fluid comes into direct contact with eyes immediately flush with plenty of water. If irritation develops seek medical advise.
Skin contact	Wash hands after handling the product.
Ingestion	Not expected to present an ingestion hazard under normal conditions.

SECTION 5: Firefighting measures

5.1. Extinguishing media

	Carbon dioxide (CO2). Foam. Water spray.
--	--

5.3. Advice for firefighters

	Protective equipment.
--	-----------------------

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

	Avoid direct contact of the impregnating fluid with the eyes.
--	---

6.2. Environmental precautions

	Do not empty into drains; dispose of this material and its container in a safe way.
--	---

6.3. Methods and material for containment and cleaning up

	Absorb any impregnating fluid onto suitable inert material and collect spilled product for subsequent disposal. Empty containers can be sent for disposal or recycling. Treat as Industrial Waste.
--	--

SECTION 7: Handling and storage

7.1. Precautions for safe handling

	Avoid direct contact of the impregnating fluid with the eyes.
--	---

7.2. Conditions for safe storage, including any incompatibilities

Suitable packaging	Store in original container under normal warehouse conditions.
--------------------	--

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. Exposure Limit Values

Propan-2-ol	WEL 8-hr limit ppm: 400 WEL 15 min limit ppm: 500	WEL 8-hr limit mg/m3: 999 WEL 15 min limit mg/m3: 1250
-------------	--	---

8.2. Exposure controls

8.2.1. Appropriate engineering controls	Not normally required.
Eye / face protection	None required under normal conditions of use.

Klenzeen Hard Surface Wipes

SD0811 v1.0 RS 481-648

Revision 0

Revision date 2011-09-01

8.2. Exposure controls

Skin protection -
Handprotection

For prolonged or repeated skin contact use suitable protective gloves.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State Solid

SECTION 10: Stability and reactivity

10.2. Chemical stability

This preparation is stable under normal conditions of storage/use and no chemical incompatibility is known.

SECTION 11: Toxicological information

11.1.4. Toxicological Information

Alkyl(C12-16)dimethylbenzylam
monium chloride

Oral Rat LD50: 400

SECTION 12: Ecological information

12.1. Toxicity

No data available

SECTION 13: Disposal considerations

Disposal methods

Dispose of the preparation according to local and national regulations.
The container and case if applicable can be recycled, please contact supplier.

SECTION 14: Transport information

ADR/RID

The product is not classified as dangerous for carriage.

IMDG

The product is not classified as dangerous for carriage.

IATA

The product is not classified as dangerous for carriage.

SECTION 15: Regulatory information

Labelling

Risk phrases

No Significant Hazard.

Safety phrases

S2 - Keep out of the reach of children.

S25 - Avoid contact with eyes.

S26 - In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

SECTION 16: Other information

Other information

Text of risk phrases in Section
3

R11 - Highly flammable.

R21/22 - Harmful in contact with skin and if swallowed.

R34 - Causes burns.

R36 - Irritating to eyes.

R50 - Very toxic to aquatic organisms.

R67 - Vapours may cause drowsiness and dizziness.

General information

The information supplied in this Safety Data Sheet is designed only as guidance for the safe use,

Klenzeen Hard Surface Wipes

SD0811 v1.0 RS 481-648

Revision 0

Revision date 2011-09-01

General information

	storage and handling of the product. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	---
