



Connectors > Pluggable IO Connectors & Cages



Form Factor: **SFP+**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	SFP+
Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Ports	4
Port Matrix Configuration	1 x 4

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Body Features

Heat Sink Style	Pin
Heat Sink Height	13.5 mm[.531 in]
Heat Sink Height Class	Networking Tall

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Housing Features

Cage Material	Nickel Silver
---------------	---------------



Dimensions

PCB Thickness (Recommended)	2.25 mm[.089 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	SFP+ Enhanced
Heat Sink Compatible	Yes
Circuit Application	Signal

Packaging Features

Packaging Method	Package
------------------	---------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2170068-1 SFP+ 1x4 Light Pipe Assembly Low Profile	 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # 2142970-7 CABLE ASSY, MICRO SFP+ TO STD SFP+, 6M	 TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG
 TE Part # 2007099-4 SFP+ 1x4 Light Pipe Assembly	 TE Part # CAT-C11-H5062 SFP+ to SFP+ I/O Cable Assembly: 28 AWG	 TE Part # 2142970-2 CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M	 TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG
 TE Part # 2142970-4 CABLE ASSY, MICRO SFP+ TO STD SFP+, 3M	 TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG
 TE Part # 2142970-3 CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG



TE Part # 2142970-6
CABLE ASSY, MICRO SFP+ TO STD SFP+, 5M



TE Part # 2142970-5
CABLE ASSY, MICRO SFP+ TO STD SFP+, 4M




TE Part # 2185251-4
STG TL SFP+ ENHANCED 1X4 HS LP SFP+, 4M


Customers Also Bought



TE Part #2-1445057-3
MICRO MNL HDR ASSY SINGLE ROW



TE Part #5-2176238-6
CPF A 0805 25K 0.1% 25PPM 5K RL



TE Part #1-216093-6
AMP-LATCH PRE-ASSY DIL WITHO



TE Part #350218-2
UMNL PIN 20-14 .0126AUBR




TE Part #1735443-2
Assembly Micro SATA Plug 7P+9P




TE Part #NB16012001
RT-375-1/8-X-STK




TE Part #2013290-1
SEMI-HARD TRAY DDR3 204P 5.2H RVS



TE Part #2820833006
44A0111-28-3



TE Part #2198230-4
SFP+ Enhanced 1x2, Networking Heatsink



TE Part #114134-E
ERMB22 110 FS 1 EE * 3,70 A-E V-V * * 24

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2149730-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2149730-4_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2149730-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English