



## INTENSIVE LONG STRAIGHT GRINDER

6 MM

**RC1652P**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:10





## DESCRIPTION

### INTENSIVE LONG STRAIGHT GRINDER 6 MM

**POWERFUL** With a power rating of 740 W for 19,500 rpm, the time factor is the main criteria when it comes to choosing this equipment. The time saving obtained has been measured at 25% when working inside tubes. **COMFORTABLE** Specially designed for two-handed use. Its 'full hand' handle ensure an ideal position with the secure trigger. The other hand with the profiled spindle is situated perfectly in the axis making it possible to use the machine at full power by pressing perfectly on the part you are working on. Proposed on the basis of the PTS 1651P and 1653P, this two-hand grinder is equipped with a long spindle to facilitate difficult-to-access jobs, notably inside tubes. It is much sought-after by metalworkers and locksmiths, etc. for repetitive or large-scale tasks. Optimum working torque 740 W/ 19,500 rpm. Sheathed casing handle insulating against the cold. Rear exhaust. Regulator and secure control lever.

## STANDARDS / DIRECTIVES

2006/42/CE, ISO 15744, ISO 28927-2

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:10



SPECIFIC DATA

Designation	INTENSIVE LONG STRAIGHT GRINDER 6 MM
Sales reference	RC1652P
L (mm)	330
Weight (g)	1630
l (mm)	45
h (mm)	45
Power (W)	19 500
Rotation speed (rpm)	2,5
Vibration (m/s <sup>2</sup> )	79
Noise level (dBa)	6,2
C mm	1/4"
C min mm	
C mm	M2   SAM Equipment and Machine Guarantee
C mm	
Guarantee	

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

