

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Your advantages

- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- ✓ Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon



Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 5 5 6 2 6 2 1 2 2 9 6
GTIN	4055626212296
Weight per Piece (excluding packing)	59.500 g
Custom tariff number	39199080
Country of origin	China
Sales Key	BG241E

Technical data

Dimensions

Length (b)	8000 mm
Width (a)	12 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 75 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

General

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952

Technical data

General

Color	green
Components	Free from silicone and cadmium
Material	Vinyl polymer
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281103
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952

Classifications

ETIM

ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504