Technical sheet

BTC60STOP

Modular barrier Ø 60 mm - stop post for gate

Modular warehouse barrier designed to ensure safety in industrial areas. It helps to organise vehicle traffic and demarcate high-risk zones, whilst ensuring the protection of people. Made from galvanised steel and coated with yellow epoxy paint. These various components allow for the creation of 'customized' paths:

- Available in 40 mm or 60 mm diameter tubing,
- Various post types: straight, corner, 2-sided or 3-sided,
- Various gate types: wicket gate or swing gate

Fixings available as options.





Customs code	7326909890
EAN	3321360116796

Color : Yellow

Material : Galvanized steel

Specifications :

- Stop post for swing gates in modular barrier systems.
- Compatible with the BTC60POR swing gate to secure the gate in the closed position.
- Option to add a 10 mm diameter padlock (optional) to block the passage.
- Tube diameter: 60 mm.
- Mounting plate: 60 x 150 mm.
- 4 mounting holes: 14 mm diameter.
- Fixings optional.
- Do not install in saline or hydrocarbon environments.

Length (mm)	Width (mm)	Height (mm)	Dimensions plate (mm)	Net weight (kg)
330	170	1000	170 x 80	4,00

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com