

Technical data


1207SC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	35 mm
D - External diameter	72 mm
B - Bearing/Inner ring width	17 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	C3
Precision class	P0
Mass	0,33 kg

PRODUCT PERFORMANCE

C - Dynamic load	15900000 mN
C0 - Static load	5100000 mN
Cu - Fatigue limit load	210000 mN
e - Coefficient	0.23
Y0 - Static axial load coefficient	2.8
Y1 - Lower axial load coefficient	2.7
Y2 - Upper axial load coefficient	4.2
N lim - Oil lubrication limit speed	60000 °/s
N lim - Grease lubrication limit speed	51000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	41,5 mm
Da max - Max shoulder diameter OR	65,5 mm



1207SC3
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm