


1200 V, 5 A power Schottky high surge silicon carbide diode



Features

- None or negligible reverse recovery
- Switching behavior independent of temperature
- Robust high voltage periphery
- Operating T_j from $-55\text{ }^{\circ}\text{C}$ to $175\text{ }^{\circ}\text{C}$
- DPAK HV creepage distance (anode to cathode) = 3 mm min.
- **ECOPACK2** compliant component

Applications

- DC/DC converter
- Boost PFC
- EV Charging station

Description

The SiC diode, available in DPAK HV 2L, is an ultrahigh performance power Schottky rectifier. It is manufactured using a silicon carbide substrate. The wide band-gap material allows the design of a low V_F Schottky diode structure with a 1200 V rating. Thanks to the Schottky construction, no recovery is shown during turn-off and ringing patterns are negligible. The minimal capacitive turn-off behavior is independent of temperature.

Based on latest technology optimization, this ST SiC diode has an improved forward surge current capability, and is ideal to boost the performance in hard switching conditions while bringing robustness to the design. Its high forward surge capability ensures a good robustness during transient phases.

Product label



Product status link

[STPSC5G12](#)

Product summary

$I_{F(AV)}$	5 A
V_{RRM}	1200 V
T_j (max.)	$175\text{ }^{\circ}\text{C}$
V_F (typ.)	1.35 V

1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol	Parameter			Value	Unit
V _{RRM}	Repetitive peak reverse voltage (T _j = -55 °C to +175 °C)			1200	V
I _{F(RMS)}	Forward rms current			15	A
I _{F(AV)}	Average forward current	T _c = 155 °C, δ = 1		5	A
I _{FRM}	Repetitive peak forward current	T _c = 155 °C, T _j = 175 °C, δ = 0.1, f _{sw} > 10 kHz		20	A
I _{FSM}	Surge non repetitive forward current	t _p = 10 ms sinusoidal	T _c = 25 °C	50	A
			T _c = 150 °C	37	
		t _p = 10 μs square	T _c = 25 °C	345	
T _{stg}	Storage temperature range			-65 to +175	°C
T _j	Operating junction temperature range			-55 to +175	°C

Table 2. Thermal resistance parameters

Symbol	Parameter	Value		Unit
		Typ.	Max.	
$R_{th(j-c)}$	Junction to case	1.2	1.7	°C/W

For more information you can refer to:

- [AN5088](#): Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25\text{ °C}$	$V_R = V_{RRM}$	-	2.5	37.5	μA
		$T_j = 150\text{ °C}$		-	8	125	
		$T_j = 175\text{ °C}$			18		
$V_F^{(2)}$	Forward voltage drop	$T_j = 25\text{ °C}$	$I_F = 5\text{ A}$	-	1.35	1.50	V
		$T_j = 150\text{ °C}$		-	1.75	2.10	
		$T_j = 175\text{ °C}$			1.90		

1. Pulse test: $t_p = 10\text{ ms}$, $\delta < 2\%$

2. Pulse test: $t_p = 380\text{ }\mu\text{s}$, $\delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.924 \times I_{F(AV)} + 0.235 \times I_F^2 (RMS)$$


For more information, refer to the following application notes related to the power losses:

- [AN604](#): Calculation of conduction losses in a power rectifier
- [AN4021](#): Calculation of reverse losses on a power diode

Table 4. Dynamic electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$Q_{Cj}^{(1)}$	Total capacitive charge	$V_R = 800 \text{ V}$	-	26	-	nC
C_j	Total capacitance	$V_R = 0 \text{ V}, T_c = 25 \text{ }^\circ\text{C}, F = 1 \text{ MHz}$	-	380	-	pF
		$V_R = 800 \text{ V}, T_c = 25 \text{ }^\circ\text{C}, F = 1 \text{ MHz}$	-	20	-	

1. Most accurate value for the capacitive charge: $Q_{Cj}(V_R) = \int_0^{V_R} C_j(V) dV$

Figure 1. Thermal transient impedance model circuit of the diode – $Z_{th(j-c)}$

Table 5. Components typical values of the diode thermal transient impedance model $Z_{th(j-c)}$

Ref.	Value (K/W)	Ref.	Value (J/K)
R_{th1}	53.54 m	C_{th1}	0.45 m
R_{th2}	441.7 m	C_{th2}	0.38 m
R_{th3}	446.8 m	C_{th3}	1.36 m
R_{th4}	209.25 m	C_{th4}	6.38 m
R_{th5}	49.71 m	C_{th5}	80.13 m

1.1 Characteristics (curves)

Figure 2. Forward voltage drop versus forward current (typical values)




Figure 3. Reverse leakage current versus reverse voltage applied (typical values)




Figure 4. Peak forward current versus case temperature ($f_{sw} > 10$ kHz)




Figure 5. Junction capacitance versus reverse voltage applied (typical values)




Figure 6. Relative variation of thermal impedance junction to case versus pulse duration




Figure 7. Non-repetitive peak surge forward current versus pulse duration (sinusoidal waveform)






Figure 8. Total capacitive charges versus reverse voltage applied (typical values)

Figure 9. Thermal resistance junction to ambient versus copper surface under tab (typical values)



2 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 DPAK HV 2L package information

- Epoxy meets UL 94,V0
- Cooling method: by conduction (C)

Figure 10. DPAK HV 2L package outline




8398255_B_10

Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 6. DPAK HV 2L package mechanical data

Ref.	Dimensions					
	Millimeters			Inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.20	2.29	2.40	0.086	0.090	0.095
A1	0.90		1.10	0.035		0.044
A2	0.03		0.23	0.001		0.010
b	0.64	0.76	0.90	0.025	0.030	0.036
b4	5.20	5.30	5.40	0.201	0.204	0.213
c	0.45		0.60	0.017		0.024
c2	0.48		0.60	0.018		0.024
D	6.00		6.20	0.236		0.245
D1	4.60	4.70	4.80	0.181	0.185	0.189
E	6.40		6.60	0.251		0.260
E1	4.95	5.10	5.25	0.194	0.201	0.207
e	2.16	2.28	2.40	0.085	0.090	0.095
e1	4.40		4.60	0.173		0.182
H	9.35		10.10	0.368		0.398
L	1.00		1.50	0.039		0.060
L1	2.60	2.80	3.00	0.102	0.110	0.119
L2	0.65	0.80	0.95	0.025	0.031	0.038
V2	0°		8°	0°		8°

Figure 11. Footprint (dimensions in mm)


8398255_B_FP_10

Note: For package and tape orientation, reel and inner box dimensions and tape outline see [TN1173](#).

2.2 Creepage distance between anode and cathode

Table 7. Creepage distance between anode and cathode

Symbol	Parameter		Value	Unit
Cd _{A-K}	Minimum creepage distance between A and K	DPAK HV	3.0	mm

Note: DPAK HV creepage distance (anode to cathode) = 0.3 mm min. (refer to IEC 60664-1)

3 Ordering information

Table 8. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPSC5G12B2-TR	PSC5G12B2	DPAK HV 2L	0.346 g	2500	Tape and reel

Revision history

Table 9. Document revision history

Date	Revision	Changes
21-Oct-2025	1	Initial release.

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved