

Product datasheet

Specifications



circuit breaker ComPacT NSX100M
AC/DC, 40 kA at 240 VAC, TMD trip
unit 100 A, 1 pole 1d

C10M1TM100

EAN Code: 3606481995803

Main

Range	ComPacT
product name	ComPacT NSX
Device short name	NSX100M
Product or component type	Circuit breaker
Device application	Distribution
Poles description	1P
Protected poles description	1D
[In] rated current	100 A at 40 °C
[Ue] rated operational voltage	277 V AC 50/60 Hz 250 V DC 50/60 Hz
Network type	AC DC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 250 V DC conforming to IEC 60947-2
Performance level	M 40 kA 240 V AC
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit protection functions	LI
control type	Toggle
Circuit breaker mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 250 V DC conforming to IEC 60947-2
Mechanical durability	20000 cycles
Electrical durability	20000 cycles at 277 V In/2 10000 cycles at 277 V In
Power dissipation per pole	8.8 W

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	Backplate
Mounting position	Horizontal and vertical Flat on the back
Upside connection	Front
Downside connection	Front
Connection pitch	35 mm
Protection type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip unit rating	100 A at 40 °C
Long-time pick-up adjustment type Ir (thermal protection)	Fixed
[Ir] long-time protection pick-up adjustment range	1 x In
Long-time protection delay adjustment type tr	Fixed
Instantaneous protection pick-up adjustment type Ii	Fixed
[Ii] instantaneous protection pick-up adjustment range	800 A
Earth-leakage protection	Without
Width (W)	35 mm
Height (H)	161 mm
Depth (D)	86 mm
Net weight	0.7 kg

Environment

Standards	EN/IEC 60947-2
Overvoltage category	Class II
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	13.000 cm
Package 1 Length	17.000 cm
Package 1 Weight	710.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	12

Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.940 kg
Unit Type of Package 3	P12
Number of Units in Package 3	96
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	83.520 kg

Logistical informations

Country of origin	PL
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	53
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	3874e08b-fcb8-4aa9-87c4-d36abebf2833
REACH Regulation	REACH Declaration
Halogen content performance	Product contains halogen above thresholds
PVC free	Yes

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

