




MBC33-12-12-A

Ruland MBC33-12-12-A, 12mm x 12mm Bellows Coupling, Aluminum, Clamp Style, 33.3mm OD, 42.9mm Length



Description

Ruland MBC33-12-12-A is a bellows coupling with 12mm x 12mm bores, 33.3mm OD, and 42.9mm length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. MBC33-12-12-A is comprised of two anodized aluminum hubs and a stainless steel bellows. The bellows are able to flex while remaining rigid under torsional loads allowing for all types of misalignment to be accommodated. This bellows coupling is lightweight and has low inertia making it suitable for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MBC33-12-12-A to be torsionally rigid and an excellent fit for precise positioning stepper servo applications as well as encoders. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS2 and REACH compliant. MBC33-12-12-A is carefully manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Large Bore B1	12 mm	Small Bore B2	12 mm
B1 Shaft Penetration	20.4 mm	B2 Shaft Penetration	20.4 mm
Outer Diameter OD	33.3 mm	Bore Tolerance	+0.03 mm / -.00 mm
Length L	42.9 mm	Hub Width LH	15.00 mm
Forged Clamp Screw	M3	Screw Material	Alloy Steel
Hex Wrench Size	2.5 mm	Screw Finish	Black Oxide
Seating Torque	2.1 Nm	Number of Screws	2 ea
Static Torque	13.6 Nm	Angular Misalignment	1.5°
Dynamic Torque Non-Reversing	6.80 Nm	Parallel Misalignment	0.15 mm
Dynamic Torque Reversing	3.40 Nm	Axial Motion	0.40 mm
Torsional Stiffness	45 Nm/Deg	Maximum Speed	10,000 RPM
Material Specification	Hubs: 2024-T351 Aluminum Bar Bellows: Type 321 Stainless Steel	Temperature	-40°F to 200°F -40°C to 93°C
Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize	Country of Origin	USA
Weight (lbs.)	0.1650	UPC	63452906386
Note 1	Stainless steel hubs are available upon request.		
Note 2	Torque ratings are at maximum misalignment.		
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the metal bellows. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the metal bellows. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the metal bellows. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.		