

KSA1000EV4254

Vertical distribution length, Canalis KSA1000, aluminium, 1000A, fixed length 2.5m, 4 outlets, 3L+N+PE, white RAL9001



Main

Range	Canalis
Device short name	KSA
Offer type	Rising main
Product or component type	Busbar trunking
Busbar description	Vertical distribution length
Product compatibility	Canalis KSA busbar trunking 500...1000 A
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
Number of tap-off outlets	4
[Ie] rated operational current	1000 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
Mounting mode	By screws
Dimension type	Fix
Length	2.5 m
Colour	White (RAL 9001)

Complementary

Number of poles	4
Neutral position	Right
Mounting position	Vertical
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	690 V
[Icw] rated short-time withstand current	37.4 kA
[Ipk] rated peak withstand current	78.7 kA
Electrical connection	Lubricated sliding contact
Width	113 mm
Height	146 mm
Net weight	44 kg
Tap-off unit interval	500 mm
Radiated magnetic field	1.27 µT
Thermal stress limit	1758000 kA².s
THDI	0...15 % 1000 A 15...33 % 800 A 33...100 % 630 A
Maximum voltage drop	<0.005 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.007 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.007 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.008 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	IEC 61439-1 IEC 61439-6

Environment

IK degree of protection	IK08 conforming to IEC 62262
Ambient air temperature for operation	35 °C (without derating) 55 °C (with derating factor)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins