


Neodymium Disc Magnet datasheet

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



Product Information

Product No.	Diameter <i>mm</i>	Height* <i>mm</i>	Weight <i>kg</i>	Pull force
N700-RB	3	2	0.0001	0.3
N701-RB	6	6	0.0008	1.3
N702-RB	9	3	0.0014	1.6
N703-RB	10	5	0.0029	2.7
N801	4	2	0.0002	0.4
N802	4	3	0.0003	0.7
N805	5	3	0.0004	0.85
N807	6	3	0.0006	1.0
N808RS	6	4	0.0008	1.3
N809	8	4	0.0015	1.7
N812	10	3	0.0018	1.65
N814	15	3	0.0040	2.5
N815	20	3	0.0071	3.3
N816	20	10	0.0236	10.5

*magnetic axis