




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold (Au)**
Wire Contact Termination Area Plating Material: **Tin**
Operating Voltage: **300 VAC**
Wire Size: **26 – 22 AWG**

Features

Product Type Features

Applied Pressure	Standard
------------------	----------

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	300 VAC

Contact Features

Contact Underplating Material	Nickel
Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Material Finish	Bright
Wire Contact Termination Area Plating Thickness	1.27 – 2.54 μm[50 – 100 μin]
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Tin



Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter Range	.91 – 1.37 mm[.035 – .054 in]
Wire Size	254 – 642 CMA

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
---	-----------------------

Packaging Features

Packaging Quantity	12500
Packaging Method	Strip

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151236-2
OCEAN_2.0_Applicator-S-042F055O-RSA

TE Part # 7-2151236-7
OCEAN_2.0_SPARE_PART_KIT-042F055O

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

TE Part # 2151236-1
OCEAN_2.0_Applicator-S-042F055O-RSM

TE Part # 843477-1
TOOL, EXTRACTION RESET

TE Part # 91531-1
CCII MTE AMPMODU MTE PIN REC 26-22 ASSY

Also in the Series | AMPMODU MTE

Board-to-Board Headers & Receptacles(24)

Connector Caps & Covers(18)

Connector Contacts(27)

Connector Hardware(1)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(444)



Wire-to-Board Connector Assemblies & Housings(298)



Wire-to-Board Headers & Receptacles (420)

Customers Also Bought



TE Part #66564-8
III+ PIN,24-20,30AU/FL,STRIP



TE Part #643182-2
UMNL STR/REL ADAPTER CAP



TE Part #208485-1
CMC RECPT ASSEMBLY SIZE 28



TE Part #66100-4
III+ SKT,18-16,30AU/FL,STRIP



TE Part #66106-7
III+ PIN,26-24,15AU/FL,STRIP



TE Part #66102-3
III+ PIN,24-20,15AU/FL,STRIP



TE Part #66564-6
III+ PIN,24-20,TIN-LEAD,STRIP



TE Part #66563-6
III+ SKT,24-20,TIN-LEAD,STRIP



TE Part #770084-1
05P .093 COMM P&S PLUG HSG



TE Part #ZPF000000000102762
787-8055-10M

Documents

Product Drawings
MTE PIN 22-26 AWG PLTD
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-104505-0_V.2d_dxf.zip
English
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-104505-0_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-104505-0_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPMODU MTE INTERCONNECT SYSTEM](#)

English

Product Specifications

[Application Specification](#)

English