




Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **130 Newton**
Product Length: **290 mm [11.4 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	130 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	80 mm[3.15 in]
Product Length	290 mm[11.4 in]
Product Width	3.6 mm[.141 in]
Product Thickness	1.3 mm[.051 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-160967-1
[CABLE TY 98X2.5 NAT](#)

Customers Also Bought


TE Part #3-643817-2
[02P MTA156 CONN ASSY 18AWG ORA](#)

TE Part #640445-3
[03P MTA156 HDR ASSY FL/STR SN](#)

TE Part #640445-4
[04P MTA156 HDR ASSY FL/STR SN](#)

TE Part #735187-2
[110 FASTON TAB TPBR](#)





TE Part #2-160967-2
CABLE TY 98X2.5 BLA



TE Part #3-643817-5
05P MTA156 CONN ASSY 18AWG
ORA



TE Part #CAT-104MTA-NTPNR
MTA Receptacle: Nylon, Tin Plated,
2.54 mm



TE Part #3-643817-4
04P MTA156 CONN ASSY 18AWG
ORA



TE Part #640445-2
02P MTA156 HDR ASSY FL/STR SN

Documents

Product Drawings

CABLE TY 290X3.6 BLA

English

Datasheets & Catalog Pages

Connectivity Solutions for Industrial Applications

English

CABLE TIES

English