



Main

Range of product	Opale
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Nb of 18 mm modules per row	13
Nb of horizontal rows	1
Provided equipment	Phase and neutral terminal blocks (2) Phase and neutral terminal block support (1) Earth terminal block (1) Blanking plate (1) Marking kit (1)
Width	252 mm
Height	225 mm
Depth	106 mm

Complementary

Enclosure mounting	Surface
Total number of 18 mm modules	13
[In] rated current	63 A
Type of rail	DIN
Cable entry	4 knock-outs
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	1 earth terminal block with 15 2 phase / neutral terminal block with 4
Distribution block outgoers	6 x 16 mm ² for phase / neutral 3 x 25 mm ² for earth 2 x 25 mm ² for phase / neutral 12 x 2.5 mm ² for earth
Locking options description	1 keylock + 1 key
Enclosure material	Self-extinguishing material
Colour	Enclosure : white (RAL 9003)

Environment

Standards	NF C 61-910
Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to NF EN 60529
IK degree of protection	IK07 conforming to NF EN 50102

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Period	18 months
--------	-----------
