



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **Protective Relay**

Current Type: **DC**

Contact Arrangement: **2 Form C DPDT-CO**

Contact Current Rating: **5 A**

Main Termination & Connection Type: **Screw Terminals**

Features

Product Type Features

Relay & Contactor Type	Protective Relay
------------------------	------------------

Configuration Features

Phase	Three
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Input Voltage	18 – 54 VDC
Contact Current Rating	5 A

Signal Characteristics

Frequency Adjustment	50 – 400 Hz
----------------------	-------------

Termination Features

Main Termination & Connection Type	Screw Terminals
Coil Termination & Connection Type	Screw Terminals

Mechanical Attachment

Product Mounting Feature Type	Mounting Hole, Snap-On
Product Mount Type	DIN Rail

Dimensions

Product Width	73 mm[2.87 in]
Product Length	75 mm[2.95 in]



Product Height	112 mm[4.41 in]
----------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 60 °C[-40 – 140 °F]
Environmental Ambient Temperature (Max)	60 °C[140 °F]

Operation/Application

Protection Function	Phase Sequence
Current Type	DC

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # 2-1618058-3
WD47-002=RELAY PHASE SEQUENCE



TE Part # 2-1618058-4
WD47-003=RELAY PHASE SEQUENCE

Also in the Series | Kilovac WD



AC Relays(7)


Customers Also Bought



TE Part #2-1532173-7
M83513/04-C11C, MCKS-C2-B-21S6Q9-18.0




TE Part #YDTS20W21-16AAV001
RECP ASSY



TE Part #2842282-6
6P,2MM,SHRD HDR,DRVT,0.1AU,TB



TE Part #YDTS20W15-97BNV001
RECP ASSY



TE Part #2-1617561-0
3SBC1668A2=M39016/38-008L



TE Part #EK4876-000
91H3-25-16-1-C-HE300



TE Part #1-1618058-0
WD2759-001=OVER /UNDervoltage R

TE Part #188434-000
382C322-50-0



TE Part #YDTS20W23-35BCV001
RECP ASSY



TE Part #A82239-000
MTCPOKT1P2SGAD



Documents

Product Drawings

WD47-001=RELAY PHASE SEQUENCE

English

Datasheets & Catalog Pages

5-1773450-5_sec11_KILOVAC_WD

English