



Product data sheet

Power tools for trade & industry

HGS 77/50

INDUSTRIAL HGS 77/50

Straight handle, central drive end

The most important data

Permitted grinding stone diameter	50 mm
No-load speed	18,000 rpm
Rated power, output	1,050 W

Part Number 0 602 211 434



Technical data

Technical data

Frequency	300 Hz
Voltage	200 V
Permitted grinding stone diameter	50 mm
No-load speed	18,000 rpm
Rated power, input	1,450 W
Rated power, output	1,050 W
Rated current	5.5 A
Weight as per EPTA	5.4 kg
Toolholder, drive end	Collet 8 mm
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

