

FAG


24024-BE-XL-C3

Spherical Roller Bearing

Spherical roller bearing 240...-BE-XL,
symmetric with rib washer


X-life

Technical information



Your current product variant

Design	BE	with lose center lip ring
Bore type	Z	Cylindrical
Cage	JPB	Sheet metal cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication feature	Standard	



Main Dimensions & Performance Data

d	120 mm	Bore diameter
D	180 mm	Outside diameter
B	60 mm	Width
C _r	450,000 N	Basic dynamic load rating, radial
C _{0r}	690,000 N	Basic static load rating, radial
C _{ur}	86,000 N	Fatigue load limit, radial
n _G	3,450 1/min	Limiting speed
n _{gr}	2,360 1/min	Reference speed
≈m	5.256 kg	Weight



Mounting dimensions

d _{a min}	128.8 mm	Minimum diameter shaft shoulder
D _{a max}	171.2 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	159.8 mm	Bore diameter outer ring
d ₂	134.5 mm	Raceway diameter of the inner ring
d _s	3.2 mm	Diameter lubrication hole
n _s	6.5 mm	Width of lubricating groove

Temperature range









T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0.29	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2.33	Dynamic axial load factor
Y ₂	3.47	Dynamic axial load factor
Y ₀	2.28	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment