

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name: RENOLIT EP 2

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Lubricating grease

Uses advised against: No uses advised against identified.

1.3 Details of the supplier of the safety data sheet

Manufacturer / Supplier FUCHS LUBRICANTS (UK) PLC.
New Century Street
ST1 5HU Hanley
Telephone: +44 (0) 1782 203700

Contact Person: Product Safety department
E-mail: product.safety@fuchs.com
Telephone: +44 (0) 1782 203700

1.4 Emergency telephone number: UK NHS: Dial 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

The product has been classified and labelled as hazardous according to regulation GB-CLP.

Classification according to GB-CLP.

Health Hazards

Skin sensitizer	Category 1	H317: May cause an allergic skin reaction.
-----------------	------------	--

Environmental Hazards

Chronic hazards to the aquatic environment	Category 3	H412: Harmful to aquatic life with long lasting effects.
--	------------	--

Hazard summary

Physical Hazards: No data available.

2.2 Label Elements

Contains: carboxylic acid zinc salt

Product name: RENOLIT EP 2



Signal Words: Warning

Hazard Statement(s): H317: May cause an allergic skin reaction.
H412: Harmful to aquatic life with long lasting effects.

Precautionary Statements

Prevention: P273: Avoid release to the environment.
P280: Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response: P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

Disposal: P501: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

Supplemental label information

EUH208: Contains: Tolutriazole derivative. May produce an allergic reaction.

2.3 Other hazards: By handling of mineral oil products and chemical products no particular hazard is known when normal precautions (item 7) and personal protective equipment (item 8) are kept. The product may not be released into the environment without control.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

General information: Lubricating grease: Thickener system and additives in solvent refined mineral oil.

Chemical name	Identifier	Concentration *	UK-REACH Registration No.	Notes
carboxylic acid zinc salt	EINECS: 282-762-6	1,00% - <5,00%		
organic Polysulphide	EINECS: 273-103-3	0,10% - <1,00%		
amine phosphate	EINECS: 931-384-6	0,10% - <1,00%		
Tolutriazole derivative	EINECS: 939-700-4	0,10% - <1,00%		
alkenyl amine, long-chain	EC: 627-034-4	0,01% - <0,25%		

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

Product name: RENOLIT EP 2

Classification

Chemical name	Identifier	Classification
carboxylic acid zinc salt	EINECS: 282-762-6	GBCLP: Aquatic Chronic 3;H412, Skin Sens. 1;H317, Eye Irrit. 2;H319
organic Polysulphide	EINECS: 273-103-3	GBCLP: Skin Sens. 1B;H317, Aquatic Chronic 3;H412
amine phosphate	EINECS: 931-384-6	GBCLP: Eye Dam. 1;H318, Acute Tox. 4;H302, Skin Sens. 1;H317, Aquatic Chronic 2;H411
Tolutriazole derivative	EINECS: 939-700-4	GBCLP: Skin Irrit. 2;H315, Skin Sens. 1B;H317, Aquatic Acute 1;H400, Aquatic Chronic 2;H411
alkenyl amine, long-chain	EC: 627-034-4	GBCLP: Acute Tox. 4;H302, Asp. Tox. 1;H304, STOT SE 3;H335, STOT RE 2;H373, Skin Corr. 1B;H314, Aquatic Acute 1;H400, Aquatic Chronic 1;H410; M-Factor (aquatic acute): 10; M-Factor (aquatic chronic): 10

GB-CLP

specific concentration limit

Chemical name	Identifier	specific concentration limit	Hazard class	Hazard Category	Hazard statements
organic Polysulphide	EINECS: 273-103-3	> 46 %	Skin sensitizer	1B	H317
amine phosphate	EINECS: 931-384-6	>= 9,39 %	Skin sensitizer	1	H317
		> 50 %	Serious eye damage	1	H318
		> 50 %	Serious eye irritation	2	H319

For the wording of the listed hazard statements refer to section 16.

Please note that the mineral oils and petroleum distillates used in our products are severely refined and have a DMSO extract < 3% as measured by method IP 346 and are not classified as carcinogenic according to Nota L/ Nota N of Annex VI of Regulation GB-CLP.

SECTION 4: First aid measures
General: Instantly remove any clothing soiled by the product.

4.1 Description of first aid measures
Inhalation: Supply fresh air; consult doctor in case of symptoms.

Eye contact: Promptly wash eyes with plenty of water while lifting the eye lids.

Skin Contact: Immediately remove contaminated clothing and shoes and wash skin with soap and plenty of water. Destroy or thoroughly clean contaminated shoes. If skin irritation or an allergic skin reaction develops, get medical attention.

Ingestion: Rinse mouth thoroughly.

4.2 Most important symptoms and effects, both acute and delayed: May cause skin and eye irritation. Suspected to cause hypersensitivity and allergy.

Product name: RENOLIT EP 2

- | | |
|---|--|
| 4.3 Indication of any immediate medical attention and special treatment needed | Get medical attention if symptoms occur. |
|---|--|

SECTION 5: Firefighting measures

5.1 Extinguishing media

- | | |
|--|---|
| Suitable extinguishing media: | CO ₂ , fire extinguishing powder or fog like water spraying. Extinguish larger fires with alcohol resistant foam or spray water with suitable surfactant added |
| Unsuitable extinguishing media: | Water with a full water jet. |

- | | |
|---|---|
| 5.2 Special hazards arising from the substance or mixture: | During fire, gases hazardous to health may be formed. |
|---|---|

5.3 Advice for firefighters

- | | |
|--|---|
| Special fire-fighting procedures: | Move container from fire area if it can be done without risk. Dispose of fire debris and contaminated fire fighting water in accordance with official regulations. Collect contaminated fire fighting water separately. It must not enter drains. |
| Special protective equipment for fire-fighters: | Self-contained breathing apparatus and full protective clothing must be worn in case of fire. |

SECTION 6: Accidental release measures

- | | |
|---|---|
| 6.1 Personal precautions, protective equipment and emergency procedures: | Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep unauthorized personnel away. |
| 6.2 Environmental Precautions: | Avoid release to the environment. Prevent further leakage or spillage if safe to do so. |
| 6.3 Methods and material for containment and cleaning up: | Scrape up spillage or absorb with absorbing material. Dispose of the material collected according to regulations. Stop the flow of material, if this is without risk. |
| 6.4 Reference to other sections: | See Section 8 of the SDS for Personal Protective Equipment. See Section 7 for information on safe handling See Section 13 for information on disposal. |

SECTION 7: Handling and storage:

- | | |
|---|---|
| 7.1 Precautions for safe handling: | Provide adequate ventilation. Avoid contact with eyes, skin, and clothing. Observe good industrial hygiene practices. Do not eat, drink or smoke when working with the product. Take usual precautions when handling mineral oil products or chemical products. |
|---|---|

Product name: RENOLIT EP 2

7.2 Conditions for safe storage, including any incompatibilities: Store in original tightly closed container. Keep separate from food, feedstuffs, fertilizers and other sensitive material. Store away from incompatible materials. No special precautions necessary if used correctly. Use only containers specifically permitted for this substance/product. Protect from contamination Local regulations concerning handling and storage of waterpolluting products have to be followed.

7.3 Specific end use(s): Not applicable

Storage Class: 11, Combustible solids

SECTION 8: Exposure controls/personal protection

8.1 Control Parameters

Occupational Exposure Limits

None of the components have assigned exposure limits.

8.2 Exposure controls

Appropriate engineering controls:

Provide adequate ventilation. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information:

Wash hands before breaks and after work. Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. The usual precautionary measures should be adhered to in handling the chemicals or the mineral oil products.

Eyeface protection:

Safety glasses (EN 166) recommended during refilling. Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield.

Skin protection

Hand Protection:

Material: Nitrile butyl rubber (NBR).
Min. Breakthrough time: ≥ 480 min
Recommended thickness of the material: $\geq 0,38$ mm

Avoid long-term and repeated skin contact. Suitable gloves can be recommended by the glove supplier. Use skin protection cream for preventive skin protection. Protective gloves, where permitted in acc. to safety directions. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Other:

Do not carry cleaning cloths impregnated with the product in trouser pockets. Wear suitable protective clothing.

Respiratory Protection:

Not relevant, due to the form of the product.

Thermal hazards:

Not known.

Product name: RENOLIT EP 2

Hygiene measures: Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

Environmental Controls: No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state:	solid
Form:	Paste
Color:	Dark brown
Odor:	Characteristic
pH:	substance/mixture is non-soluble (in water)
Drop Point:	> 180 °C (IP 396)
Boiling Point:	> 250 °C
Flash Point:	Not applicable
Evaporation Rate:	Not applicable for mixtures
Flammability (solid, gas):	not determined
Explosion Limit - Upper (%):	Not applicable for mixtures
Explosion Limit - Lower (%):	Not applicable for mixtures
Vapor pressure:	Not applicable for mixtures
Relative vapor density:	Not applicable for mixtures
Density:	0,95 g/cm ³ (15 °C)
Solubility(ies)	
Solubility in Water:	Insoluble in water
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	Not applicable for mixtures
Auto-ignition temperature:	not determined
Decomposition Temperature:	not determined
Flow time	Value not relevant for classification
Explosive properties:	Value not relevant for classification
Oxidizing properties:	Value not relevant for classification
Particle characteristics:	Study technically not feasible

9.2 Other information

No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity:	Stable under normal use conditions.
10.2 Chemical Stability:	Stable under normal use conditions.
10.3 Possibility of hazardous reactions:	Stable under normal use conditions.

Product name: RENOLIT EP 2

10.4 Conditions to avoid:	Stable under normal use conditions.
10.5 Incompatible Materials:	Strong oxidizing substances. Strong acids. Strong bases.
10.6 Hazardous Decomposition Products:	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors.

SECTION 11: Toxicological information

Information on likely routes of exposure

Inhalation:	No data available.
Ingestion:	No data available.
Skin Contact:	May cause an allergic skin reaction. May cause an allergic skin reaction.
Eye contact:	No data available.

11.1 Information on toxicological effects

Acute toxicity

Oral

Product:	Not classified for acute toxicity based on available data.
Specified substance(s) organic Polysulphide	LD 50 (Rat): 6.500 mg/kg
Tolutriazole derivative	LD 50 (Rat, Female, Male): 3.313 mg/kg (OECD 401)
alkenyl amine, long-chain	LD 50 (Rat): > 300 - 2.000 mg/kg

Dermal

Product:	Not classified for acute toxicity based on available data.
-----------------	--

Inhalation

Product:	Not classified for acute toxicity based on available data.
Specified substance(s) carboxylic acid zinc salt	LC 50 (Rat, 4 h): > 42 mg/l

Skin Corrosion/Irritation:

Product:	Based on available data, the classification criteria are not met.
Specified substance(s) Tolutriazole derivative	(Rabbit): Irritating.

Serious Eye Damage/Eye Irritation:

Product:	Based on available data, the classification criteria are not met.
Specified substance(s) Tolutriazole derivative	OECD 405 (Rabbit): Not irritant.

Product name: RENOLIT EP 2

Respiratory or Skin Sensitization:

Product: Skin sensitizer: Based on available data, the classification criteria are met.
Respiratory sensitizer: Based on available data, the classification criteria are not met.

Specified substance(s)

Tolutriazole derivative , OECD 406-1 (Guinea Pig) sensitizing

Germ Cell Mutagenicity

Product: Based on available data, the classification criteria are not met.

Carcinogenicity

Product: Based on available data, the classification criteria are not met.

Reproductive toxicity

Product: Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Single Exposure

Product: Based on available data, the classification criteria are not met.

Specific Target Organ Toxicity - Repeated Exposure

Product: Based on available data, the classification criteria are not met.

Aspiration Hazard

Product: Based on available data, the classification criteria are not met.

Other adverse effects: No data available.

SECTION 12: Ecological information

General information: Not applicable

12.1 Toxicity

Acute toxicity

Product: Based on available data, the classification criteria are not met.

Fish

Specified substance(s)

carboxylic acid zinc salt LC 50 (Fish, 96 h): > 100 mg/l (OECD 203)

amine phosphate LC 50 (Fish, 96 h): 24 mg/l

Tolutriazole derivative LC 50 (Fish, 96 h): 1,3 mg/l (OECD 203)

alkenyl amine, long-chain LC 50 (Fish, 96 h): > 0,01 - 0,1 mg/l (OECD 203)

Aquatic Invertebrates

Specified substance(s)

carboxylic acid zinc salt EC 50 (Water Flea, 48 h): > 100 mg/l (OECD 202)

organic Polysulphide EC 50 (Water Flea, 48 h): 63 mg/l (OECD 202)

amine phosphate EC 50 (Water Flea, 48 h): 91,4 mg/l

Product name: RENOLIT EP 2

Tolutriazole derivative EC 50 (Water Flea, 48 h): 2,05 mg/l (OECD 202)

alkenyl amine, long-chain EC 50 (Water Flea, 48 h): > 0,01 - 0,1 mg/l (OECD 202)

Chronic Toxicity

Product: Based on available data, the classification criteria are met.

Aquatic Invertebrates**Specified substance(s)**

amine phosphate NOEC (Water Flea, 21 d): 0,12 mg/l

alkenyl amine, long-chain NOEC (Water Flea, 21 d): 0,013 mg/l

Toxicity to Aquatic Plants**Specified substance(s)**

organic Polysulphide EC 50 (Alga, 72 h): > 101 mg/l (OECD 201)

amine phosphate EC 50 (Alga, 72 h): > 100 mg/l

Tolutriazole derivative EC 50 (Alga, 72 h): 0,976 mg/l (OECD 201)

alkenyl amine, long-chain EC 50 (Alga, 72 h): > 0,01 - 0,1 mg/l (OECD 201)

12.2 Persistence and Degradability**Biodegradation**

Product: Not applicable for mixtures

Specified substance(s)

carboxylic acid zinc salt (OECD 301B) Not readily degradable.

organic Polysulphide 13 % (28 d, OECD 301B) Not readily degradable.

Tolutriazole derivative Not readily degradable.

12.3 Bioaccumulative potential

Product: Not applicable for mixtures

12.4 Mobility in soil:

Product: Not applicable for mixtures

12.5 Results of PBT and vPvB assessment:

The product does not contain any substances fulfilling the PBT/vPvB criteria.

12.6 Other adverse effects:

Harmful to aquatic life with long lasting effects.

Water Hazard Class (WGK):

WGK 2: significantly water-endangering.

Product name: RENOLIT EP 2

SECTION 13: Disposal considerations

13.1 Waste treatment methods

General information: Dispose in accordance with all applicable regulations.

Disposal methods: Do not empty into drains; dispose of this material and its container in a safe way. When storing used products, ensure that the waste categories and mixing instructions are observed. Discharge, treatment, or disposal may be subject to national, state, or local laws. Discharge, treatment, or disposal may be subject to national, state, or local laws.

List of Waste (LoW) Codes

12 01 12*: spent waxes and fats

SECTION 14: Transport information

ADR/RID

14.1 UN number or ID number: —
14.2 UN Proper Shipping Name: —
14.3 Transport Hazard Class(es)
Class: Non-dangerous goods
Label(s): —
Hazard No. (ADR): —
Tunnel restriction code: —
14.4 Packing Group: —
14.5 Environmental hazards: —
14.6 Special precautions for user: —

IMDG

14.1 UN number or ID number: —
14.2 UN Proper Shipping Name: —
14.3 Transport Hazard Class(es)
Class: Non-dangerous goods
Label(s): —
EmS No.: —
14.3 Packing Group: —
14.5 Environmental hazards: —
14.6 Special precautions for user: —

IATA

14.1 UN number or ID number: —
14.2 Proper Shipping Name: —
14.3 Transport Hazard Class(es)
Class: Non-dangerous goods
Label(s): —
14.4 Packing Group: —
14.5 Environmental hazards: —
14.6 Special precautions for user: —

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code: Not applicable.

Product name: RENOLIT EP 2

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:

GB Regulations

The Ozone-Depleting Substances and Fluorinated Greenhouse Gases (Amendment etc.) (EU Exit) Regulations 2019:

none

The Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020:

none

15.2 Chemical safety assessment:

No Chemical Safety Assessment has been carried out.

DIRECTIVE Control of Major Accident Hazards Regulations 2015:

Not applicable

SECTION 16: Other information

Revision Information:

Vertical lines in the margin indicate an amendment.

Wording of the H-statements in section 2 and 3

H302	Harmful if swallowed.
H304	May be fatal if swallowed and enters airways.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H373	May cause damage to organs through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Other information:

The classification complies with the current GB lists; however, it has been supplemented with expert literature information and information provided by/about our company. The following evaluation methods were used: On the basis of test data; Calculation Method; Bridging Principle "Substantially similar mixtures"; Expert Judgement

Revision Date:

23.07.2024

Product name: RENOLIT EP 2

Disclaimer:

The data contained in this safety data sheet are based on our current knowledge and experience and are given to the best of our knowledge and belief. It characterizes the product only with regard to safety requirements for handling, transport and disposal. The data do not describe the product's properties (tech. product specification). Neither should any agreed property nor the suitability of the product for any specific technical application be deduced from the data contained in this safety data sheet. Modifications on this document are not allowed. The data are not transferable to other products. In the case of mixing the product with other products or in the case of processing, the data in this safety data sheet are not necessarily valid for the new-made material. It is the responsibility of the recipient of the product to observe federal, state and local law. Please contact us to obtain up-to-date safety data sheets. This document was issued electronically and has no signature.