

Eaton 266475

Catalog Number: 266475

Eaton Moeller series NZM - Molded Case Circuit Breaker. Shunt release, 208-240VAC/DC, +1early N/O, 4



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM release	266475
EAN	Product Length/Depth
4015082664756	107 mm
Product Height	Product Width
51 mm	64 mm
Product Weight	Compliances
0.266 kg	IEC
	UL/CSA
	RoHS conform

Certifications

CSA (File No. 22086)
CSA certified
UL489
IEC60947
UL (File No. E140305)
CE marking
UL listed
UL (Category Control Number DIHS)
CSA (Class No. 1437-01)
CSA-C22.2 No. 5-09

Product specifications

Used with

NZM4(-4), N(S)4(-4)

Type

Accessory

Shunt release

Special features

Cannot be used in conjunction with NZM...-XR... remote operator. If the shunt trip is live, contact with the circuit breaker's primary contacts is prevented when switched on.

Early make of auxiliary contact on switching on (manual operation): approx. 90 ms.

Shunt releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XU... undervoltage release.

Voltage rating

0.7 - 1.1 x Us

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM4](#)

Drawings

[eaton-circuit-breaker-auxiliary-contact-nzm-shunt-release-3d-drawing.eps](#)

eCAD model

[ETN.NZM4-XAHIV208-250AC_DC](#)

Installation instructions

[eaton-circuit-breaker-voltage-release-nzm4-il012143zu.pdf](#)

[eaton-circuit-breaker-voltage-release-nzm4-il01210005z.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Electric connection type

Screw connection

Fitted with:

Early-make auxiliary contact

Frame

NZM4

Frequency rating

50 Hz / 60 Hz / 200 Hz / 400 Hz, DC (shunt release)

Minimum command time - max

15 ms

Minimum command time - min

10 ms

Number of contacts (normally open contacts)

1

Reaction time

22 ms

Pick-up power consumption (shunt release)

2.5 VA/W

Rated control supply voltage

208 - 250 V AC/DC

Rated control supply voltage (Us) at AC, 50 Hz - max

250 V

Rated control supply voltage (Us) at AC, 50 Hz - min

208 V

Rated control supply voltage (Us) at AC, 60 Hz - max

250 V

Rated control supply voltage (Us) at AC, 60 Hz - min

208 V

Suitable for

Off-load switch

Power circuit breaker

Connection type

With bolt connection

Voltage type

AC/DC

Terminal capacity (solid/flexible conductor)

0.75 mm² - 2.5 mm² (2x) at shunt release with ferrule
18 - 14 AWG (1x) at shunt release
18 - 14 AWG (2x) for undervoltage releases, off-delayed
0.75 mm² - 2.5 mm² (1x) at shunt release with ferrule
18 - 14 AWG (1x) for undervoltage releases, off-delayed
0.75 mm² - 2.5 mm² (2x) for undervoltage releases, off-delayed
with ferrule
0.75 mm² - 2.5 mm² (1x) for undervoltage releases, off-delayed
with ferrule
18 - 14 AWG (2x) at shunt release

Rated control supply voltage (Us) at DC - max

250 V

Rated control supply voltage (Us) at DC - min

208 V

Voltage rating at AC (x Us) - max

1.1

Voltage rating at AC (x Us) - min

.7

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A

Time on duty - max

∞

Rated control voltage (relay contacts)

250 V DC

208 V DC

250 V AC

208 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)