



Brand of NTN corporation

Technical data

UCPLE210

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC210G2, PLE210

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	55 mm
A1 - Housing top width	36 mm
B - Width of Inner Ring	51,6 mm
d - Shaft diameter	50 mm
G - Grease fitting	M6x1



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

H - Distance mounting base to centerline spheric. seating diam.	55,6 mm
H1 - Housing foot height	19,3 mm
H2 - Housing height	114 mm
J - Mounting holes distance	164 mm
L - Housing length	214 mm
N - Mounting hole dimension	14 mm
N1 - Mounting hole length	27 mm
S - Distance front side/bearing centre	19 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	35100000 mN
C0 - Static load rating	23200000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	2,9 kg
Recommended tightening torque for set screw	22 N-m

