



**FAG****X-life****3310-BD-XL-2HRS-TVH**

Angular contact ball bearing

Angular contact ball bearing 33...-BD-XL-2HRS-TVH, double row, X-life, seals, plastic cage

Technical information



Your current product variant

Design variant	B	Bearing without filling slot
Sealing	2HRS	Contact seal on both sides
Cage	TVH	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	P6	Class6 (P6), better than PN
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Axial internal clearance	CN	Group N (CN)

n.r.

	D	Design variant
≈m	1.78 kg	Weight

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	110 mm	Outside diameter
B	44.4 mm	Width
C _r	93,000 N	Basic dynamic load rating, radial
C _{0r}	70,000 N	Basic static load rating, radial
C _{ur}	4,850 N	Fatigue load limit, radial
n _G	4,900 1/min	Limiting speed



Mounting dimensions

$d_{a\min}$	61 mm	Minimum diameter shaft shoulder
$D_{a\max}$	99 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2 mm	Maximum fillet radius

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
D_1	93.26 mm	Shoulder diameter outer ring
D_2	96.75 mm	Caliber diameter outer ring
d_1	71.47 mm	Shoulder diameter inner ring
d_2	69.05 mm	Caliber diamter inner ring
a	64.2 mm	Distance between the apexes of the pressure cones
α	30 °	Contact angle

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides